



OPTRIS CS LT IR PYROMETER, -50 to 1030 °C, 8-14 µm SPECTRAL RANGE, 0-5 VDC, 0-10 VDC, TYPE K THERMOCOUPLE OR ALARM OUTPUT, 5-30 VDC OPERATING, M12x1 THREADED END MOUNT, 8m INTEGRAL 7-CONDUCTOR SHIELDED CABLE

**OPTCSLT15SFCB8**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
5/2/2022

SHEET 1 OF 1