GS *DURAPULSE* AC DRIVES DYNAMIC BRAKING USER MANUAL TABLE OF CONTENTS

TABLE OF CONTENTS

USER MANUAL CONTENTS

WARNINGS AND TRADEMARKS W–1
DURAPULSE DYNAMIC BRAKING USER MANUAL REVISION HISTORY H–1
DURAPULSE DYNAMIC BRAKING USER MANUAL CONTENTS TOC–1
CHAPTER 1: BRAKING OVERVIEW AND COMPONENT SPECIFICATIONS 1–1
Manual Overview 1–2
Overview of this Publication 1–2
Who Should Read This Manual 1–2
Supplemental Publications 1–2
Technical Support 1–2
Special Symbols 1–3
Introduction 1–3
Dynamic Braking 1–3
Dynamic Braking Units 1–3
Braking Duty Cycle 1–4
Overload Relay 1–5
Overload Relay Purpose 1–5
Overload Relay Selection Procedure and Example 1–5
Dynamic Braking Unit Specifications 1–6
Lamp/LED Indicators for Dynamic Braking Units 1–6
CHAPTER 2: BRAKING COMPONENT INSTALLATION AND DIMENSIONS 2–1
Installation 2–2
General Installation Guidelines 2–2
Minimum Clearances and Air Flow 2–2
Braking Unit Dimensions 2–4
CHAPTER 3: BRAKING COMPONENT CONFIGURATION AND WIRING 3–1
Operational Electrical Information 3–2
Overload Relay 3–2
Dynamic Braking Unit Setup 3–3
DBU Jumper and Wiring Terminal Locations 3–3
DBU Voltage Jumper Settings 3–4
DBU Master/Slave Jumper Settings 3–5
Dynamic Braking Wiring 3–6
Wiring Warnings and Notes 3–6
Maximum Wiring Distances 3–7
Dynamic Braking Unit Wiring Terminals 3–7
Basic Braking Wiring Diagram 3–9