


C-more Part Number Cross Reference

EZTouch (as sold by AutomationDirect)		C-more *	
EZTouch 6", grayscale STN (0–45 °C)		C-more 6", grayscale STN (0–50 °C)	
	C-more 6" Adapter		
EZ-S6M-R	Requires: EA-6-ADPTR		EA7-S6M-R <--->
EZ-S6M-RS			
EZ-S6M-F	Requires: EA-6-ADPTR		EA7-S6M <---> (includes Ethernet)
EZ-S6M-FS			
EZTouch 6", 128 Color STN (0–45 °C)		C-more 6", 65,536 Color TFT (0–50 °C)	
	C-more 6" Adapter		
EZ-S6C-K	Requires: EA-6-ADPTR		EA7-T6CL-R <--->
EZ-S6C-KS			
EZ-S6C-F	Requires: EA-6-ADPTR		
EZ-S6C-FS			EA7-T6CL <---> (includes Ethernet)
EZ-S6C-FST			
EZTouch 8", 128 Color STN (0–40 °C)		C-more 8", 65,536 Color TFT (0–50 °C)	
EZ-S8C-F			EA7-T8C <---> (includes Ethernet)
EZ-S8C-FS			
EZ-S8C-FST			
EZTouch 10", 128 Color TFT (0–50 °C)		C-more 10", 65,536 Color TFT (0–50 °C)	
EZ-T10C-F			EA7-T10C <---> (includes Ethernet)
EZ-T10C-FS			
EZ-T10C-FST			
EZ-T10C-FSE			
No 12" EZTouch available		C-more 12", 65,536 Color TFT (0–50 °C)	
			EA7-T12C <---> (includes Ethernet)
EZTouch 15", 128 Color TFT (0–45 °C)		C-more 15", 65,536 Color TFT (0–50 °C)	
EZ-T15C-FS			EA7-T15C <---> (includes Ethernet)
EZ-T15C-FST			
EZ-T15C-FSE			

* Note: All C-more touch panels are NEMA 4/4X, IP65 (when mounted correctly, for indoor use only), non-FDA.