

PATLITE® Signal Devices

56mm Audible-Visual and Industrial Signal Beacon Multicolor IO-Link NE-IL Series

Overview

The NE-IL series is designed with a multicolored LED that can display up to 7 selectable LED colors (Red, Amber, Green, Blue, White, Cyan, and Purple), enabling users to color-code different statuses and equipment conditions. Two parts offer touch to acknowledge. The NE-IL series beacons are compatible with IO-Link v1.1.

Features


- Capacitive touch sensor enables real-time status confirmations
- Features simultaneous use of continuous, flashing, and audible alarm conditions
- Toggle between 4 patterns (Red, Blue, White, or off) while in touch sensor mode
- High protection rating for operation in harsh environments
- M12 connector available for quick and easy wiring
- IO-Link v1.1




56mm Audible-Visual and Industrial Signal Beacon Multicolor IO-Link NE-IL Series Selection Chart											
Part Number	Price	Type	Bulb Type	Light Function	Light Colors	Voltage	Tone Type	Tone Frequency	Touch To Acknowledge	Drawing Link	Connection*
<u>NE-ILNB-M</u>	\$123.00	Audible-visual signal beacon	Integrated LED	Selectable permanent, flashing, double flash, triple flash	Red/Amber/ Green/Blue/ White/Cyan/ Purple	24VDC	(8) selectable 88db at 1m	2.5 kHz	No	<u>PDF</u>	5-pin M12 connector A-coded
<u>NE-ILNN-M</u>	\$102.00	Industrial signal beacon	LED			24VDC	—	—	No	<u>PDF</u>	
<u>NE-ILTB-M</u>	\$151.00	Audible-visual signal beacon	Integrated LED			24VDC	(8) selectable 88db at 1m	2.5 kHz	Yes	<u>PDF</u>	
<u>NE-ILTN-M</u>	\$140.00	Industrial signal beacon	LED			24VDC	—	—	Yes	<u>PDF</u>	

* Requires a 5-pin female M12 cable, sold separately.

Wiring Diagram



M12 5-pin Connector



PATLITE® Signal Devices

56mm Audible-Visual and Industrial Signal Beacon Multicolor IO-Link NE-IL Series

Specifications

56mm Audible-Visual and Industrial Signal Beacon Multicolor IO-Link NE-IL Series Specifications					
Model		NE-ILNB-M	NE-ILNN-M	NE-ILTB-M	NE-ILTN-M
Rated Voltage		24VDC			
Operating Voltage Range		18–30 VDC			
Rated Current Consumption	Typical	80mA	40mA	80mA	40mA
	Max	100mA	50mA	100mA	50mA
Rated Power Consumption	Typical	2.0 W	1.0 W	2.0 W	1.0 W
	Max	2.4 W	1.2 W	2.4 W	1.2 W
Inrush Current		10A / 0.2 msec			
Temperature Range	Operating	-25 to 60°C [-13 to 140°F]			
	Storage	-40 to 75°C [-40 to 167°F]			
Humidity Range	Operating	Less than 90% (no condensation)			
	Storage				
Mounting		Indoor, vertical			
Insulation Resistance		More than 5MΩ at 500VDC between live part and non-current carrying metallic part			
Withstand Voltage		1 min at 500VAC between charging parts and non-charging metal parts			
Protection Rating		IP65, NEMA TYPE 4X, 13			
Weight g [oz]		100 [3.52]	90 [3.17]	100 [3.52]	90 [3.17]
Housing Material		Polycarbonate			
Agency Approval		UL 508, UR File: E215660, CSA-C22.2 No. 14			

To obtain the most current agency approval information, see the Agency Compliance & Certifications Checklist section on the specific part number's web page.

IO-Link Specifications	
IO-Link	v1.1
Port Speed	COM2 (38.4 kbps)
SIO Supported	Yes
ISDU Supported	Yes
Data Storage	Yes
Block Parameter	Yes

PATLITE® Signal Devices

56mm Visual-Audible and Industrial Signal Beacon Accessories NE-A and NE-IL Series

56mm Beacon Accessories NE-A and NE-IL Series				
Part Number	Price	Description	Weight g [oz]	Drawing Link
<u>NE-002D</u>	\$12.00	Patlite mounting bracket, wall mount, 56mm diameter, 82mm height, dark gray, polycarbonate. For use with Patlite NE-A and NE-IL series beacons.	34 [1.19]	<u>PDF</u>
<u>NE-001D</u>	\$18.50	Patlite tube adapter, tube mount, 56mm diameter, black, polycarbonate. For use with Patlite NE-A and NE-IL series beacons.	31 [1.09]	<u>PDF</u>
<u>SZP-092D</u>	\$6.50	Patlite tube adapter, tube mount, 1/2in NPT thread type, 56mm diameter, black, polycarbonate. For use with Patlite NE-A and NE-IL series beacons.	23 [0.81]	<u>PDF</u>
<u>GA0000119-F1</u>	\$10.00	Patlite O-ring, silicone. For use with Patlite NE-A and NE-IL series beacons.	45.35 [1.5]	N/A
<u>POLE-100A21</u>	\$25.50	Patlite mounting pole, 22mm diameter, 100mm length, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons.	29 [1.02]	<u>PDF</u>
<u>POLE-300A21</u>	\$28.50	Patlite mounting pole, 22mm diameter, 300mm length, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons.	86 [3.03]	<u>PDF</u>
<u>POLE-800A21</u>	\$35.50	Patlite mounting pole, 22mm diameter, 800mm length, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons.	228 [8.04]	<u>PDF</u>
<u>SZ-010</u>	\$25.50	Patlite mounting bracket, flange mount, 100mm diameter, 65mm height, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons.	122 [4.30]	<u>PDF</u>
<u>SZ-016A</u>	\$28.50	Patlite mounting bracket, flange mount, 68mm diameter, 45mm height, silver, aluminum. For use with Patlite NE-A and NE-IL series beacons.	96 [3.38]	<u>PDF</u>

[NE-002D](#)[NE-001D](#)[SZP-092D](#)[GA0000119-F1](#)[POLE-100A21](#)[SZ-010](#)[SZ-016A](#)