

Enclosure Accessories – Hole Seals and Plugs



Hole Plugs for Non-Metal Enclosures

Designed to seal extra pushbutton holes, conduit openings, and knockout openings in fiberglass enclosures from dirt, dust, oil, and water. Conduit hole sizes are nominal trade sizes, not actual hole sizes. (Example: 1 in [25 mm] conduit actual diameter = 1.315 in [33.4 mm]).

Agency Approvals

- Fiberglass hole plug for UL Types 1, 3R, 4, 4X, 6, 6P, and 12 Industrial control panel enclosures. [File E64358]
- CSA Types 1, 12, 3, 3R, 4, 4X, 6, and 6P: IEC Codes IP66, IP68 [File LR069014]



Hole Plugs for Non-Metal Enclosures				
Part Number	Price	Description	Nominal Hole Diameter Range	Wt [oz]
<u>REHPSERIES1</u>	\$7.50	Fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1/2, 5/8 and 3/4-inch hole.	0.50-0.81 [12.7-20.6]	2
<u>REHPSERIES1.5</u>	\$10.25	Fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket. For use with 1/2in conduit holes.	0.88 [22.4]	2
<u>REHPSERIES2</u>	\$8.50	Fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1/2- to 3/4-inch conduit holes and 22 or 30mm [1.18 in] pushbutton holes.	0.88-1.28 [22.4-32.5]	2
<u>REHPSERIES3</u>	\$13.75	Fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1 to 1-1/4 inch conduit holes.	1.38-1.75 [35.1-44.5]	2
<u>REHPSERIES4</u>	\$17.50	Fiberglass-reinforced polyester (FRP), closed-cell neoprene gasket, for 1-1/2 to 2-inch conduit holes.	2.00-2.56 [50.1-65.0]	2
Note: Dimensions in inches [millimeters].				



[REHPSERIES1](#)



[REHPSERIES3](#)