

# Accessories for OPT2024 - OPT2025 Photoelectric Sensors

## Right-angle Mounting Brackets

Mounting bracket, right-angle, vertical adjustment, nickel plated steel. For use with OPT2024-OPT2025 photoelectric sensors.

Mounting Brackets for OPT Series Photoelectric Sensors					
Part Number	Price	Description	Qty	Drawing Link	Weight g [oz]
<a href="#">OPT2034</a>	\$7.00	Wenglor mounting bracket, right-angle, vertical adjustment, nickel plated steel. For use with OPT2024 & OPT2025 photoelectric sensors.	1	<a href="#">PDF</a>	38 [1.34]



[OPT2034](#)

## Right-angle Swivel Mounting Systems

Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 12mm rod mount. For use with OPT2024-OPT2025 photoelectric sensors. Available in all 304 stainless steel or with an aluminum mounting head and 304 stainless steel mounting plate.

Accessories for 25mm Sensors						
Part Number	Price	Description	Mounting Head	Mounting Plate	Drawing Link	Weight [lb]
<a href="#">OPT2124</a>	\$11.50	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT2024 & OPT2025 photoelectric sensors.	Aluminum	304 Stainless Steel	<a href="#">PDF</a>	0.15
<a href="#">OPT2125</a>	\$19.00	Wenglor mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with OPT2024 & OPT2025 photoelectric sensors.	304 Stainless Steel	304 Stainless Steel	<a href="#">PDF</a>	0.27

Note: 304 Stainless steel mounting rods sold separately: [OPT2109](#) (200mm length), [OPT2110](#) (300mm length), and [OPT2111](#) (500mm length).



[OPT2124](#), [OPT2125](#)