


# ASO Safety Solutions



## SENTIR Straight Edge Safety Contact Mats




SENTIR safety contact mats are rectangular sections which are used to safeguard dangerous areas in industrial and production automation settings. Stepping on the mat triggers an immediate "stop" signal in order to prevent endangering movements.

SENTIR Straight Edge mats are designed with flexibility in mind. Two quick disconnect ends allow for easy single or multi-mat wiring in either 4-wire or 2-wire circuits with optional terminating resistor. The straight edge allows butting of additional mats and use of optional metal trim kits for securing to floor.

### Features

- Straight edge ideal for trim kits and multi-mat configurations
- Ideal for 2-wire circuits with optional terminating resistor
- Can wire in 2 or 4-wire circuits
- Male and Female quick disconnect
- Anti-slip surface
- Standard sizes available
- Available in black and yellow
- Resistant against most contaminants and moisture up to IP65




# ASO Safety Solutions




## SENTIR Straight Edge Safety Contact Mats

ASO Safety Solutions Contact Mats - Straight Edge Style					
Part Number	Price	Width (W)	Length (L)	Mat Color	Drawing
<a href="#">1602-4107</a>	\$177.00	12in [304.8 mm]	24in [609.6 mm]	Black	<a href="#">PDF</a>
<a href="#">1602-4108</a>	\$217.00	12in [304.8 mm]	36in [914.4 mm]		<a href="#">PDF</a>
<a href="#">1602-4106</a>	\$258.00	24in [609.6 mm]	24in [609.6 mm]		<a href="#">PDF</a>
<a href="#">1602-4100</a>	\$360.00	24in [609.6 mm]	36in [914.4 mm]		<a href="#">PDF</a>
<a href="#">1602-4101</a>	\$447.00	24in [609.6 mm]	48in [1219.2 mm]		<a href="#">PDF</a>
<a href="#">1602-4102</a>	\$572.00	24in [609.6 mm]	60in [1524.0 mm]		<a href="#">PDF</a>
<a href="#">1602-4103</a>	\$493.00	36in [914.4 mm]	36in [914.4 mm]		<a href="#">PDF</a>
<a href="#">1602-4104</a>	\$675.00	36in [914.4 mm]	48in [1219.2 mm]		<a href="#">PDF</a>
<a href="#">1602-4105</a>	\$789.00	36in [914.4 mm]	60in [1524.0 mm]		<a href="#">PDF</a>
<a href="#">1602-5390</a>	\$371.00	24in [609.6 mm]	36in [914.4 mm]		Yellow
<a href="#">1602-5391</a>	\$460.00	24in [609.6 mm]	48in [1219.2 mm]	Yellow	<a href="#">PDF</a>



1602-410x



ASO Safety Solutions Terminating Resistors					
Part Number	Price	Description	Use With	Contents	Drawing
<a href="#">1810-0190</a>	\$8.75	Terminating resistor, 8.2 k ohm, 3-pin male M8 connector	Safety contact mats and bumpers	1 resistor	<a href="#">PDF</a>



1810-0190


ASO Safety Contact Mat Trim Kits and Corners						
Part Number	Price	Description	Material	Use With	Contents	Drawing
<a href="#">2010-0121</a>	\$63.00	Trim kit	Aluminum	12 x 24 in safety mats	4 trim corners and 4 mat trim pieces	<a href="#">PDF</a>
<a href="#">2010-0122</a>	\$75.00	Trim kit	Aluminum	12 x 36 in safety mats	4 trim corners and 4 mat trim pieces	<a href="#">PDF</a>
<a href="#">2010-0120</a>	\$75.00	Trim kit	Aluminum	24 x 24 in safety mats	4 trim corners and 4 mat trim pieces	<a href="#">PDF</a>
<a href="#">2010-0080</a>	\$97.00	Trim kit	Aluminum	24 x 36 in safety mats	4 trim corners and 4 mat trim pieces	<a href="#">PDF</a>
<a href="#">2010-0081</a>	\$107.00	Trim kit	Aluminum	24 x 48 in safety mats	4 trim corners and 4 mat trim pieces	<a href="#">PDF</a>
<a href="#">2010-0082</a>	\$121.00	Trim kit	Aluminum	24 x 60 in safety mats	4 trim corners and 4 mat trim pieces	<a href="#">PDF</a>
<a href="#">2010-0083</a>	\$107.00	Trim kit	Aluminum	36 x 36 in safety mats	4 trim corners and 4 mat trim pieces	<a href="#">PDF</a>
<a href="#">2010-0084</a>	\$119.00	Trim kit	Aluminum	36 x 48 in safety mats	4 trim corners and 4 mat trim pieces	<a href="#">PDF</a>
<a href="#">2010-0085</a>	\$135.00	Trim kit	Aluminum	36 x 60 in safety mats	4 trim corners and 4 mat trim pieces	<a href="#">PDF</a>
<a href="#">2010-0086</a>	\$56.00	Mat trim	Aluminum	Safety contact mats	1 mat trim, 5ft [1.52 m] length	<a href="#">PDF</a>
<a href="#">2010-0087</a>	\$3.75	Trim corner	Polyamide	Safety contact mats	1 corner	<a href="#">PDF</a>



2010-0080



2010-0086



2010-0087

Straight Edge Safety Contact Mats	
	General Specifications
Height	14mm [0.55 in] with covering
Material	Polyurethane
Weight	24.9 kg/m <sup>2</sup> [5.1 lb/ft <sup>2</sup> ]
Switching Pressure	Test piece Ø 80mm [3.15 in] = approximately 150N
Inactive Edge	16mm [0.63 in]
Static Load	Max. 2,000N on Ø 80mm [3.15 in], tested according to DIN EN ISO 13856-1
Response Time	< 25ms, tested according to DIN EN ISO 13856-1
Electrical Capacity	24VDC, 100mA
Connection Cables	One cable has a 3-pin male M8 connector, and the other cable has a 3-pin female M8 connector. Cables are 4.7 in [120mm] in length
Mechanical Life	>1,000,000 cycles
Protection Class	IP65
Temperature Range	-10° to +55°C [+14° to +131°F]
Agency Approvals	CE, cULus file E329422

# Safety Products



*Warning: Safety products sold by AutomationDirect are Safety components only. The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products, used solely or in conjunction with other AutomationDirect or other vendors' products, will assure safety for any application. Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility, for the selection and suitability of the product for their respective application.*

*AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.*