

# BantamBox Series Polycarbonate Enclosures

NEMA 1, 3R, 4, 4X and 12 with Screw Cover



BB060555W



BBCC090603W

## Applications

BantamBox offers an all-polycarbonate product with clear or opaque covers. These enclosures include an external flush wall design, unobstructed internal sidewalls, 304 stainless steel cover screws, and watertight seal.

## Construction

- Polycarbonate for 1480 in-lb, high impact resistance per UL746C

## Gray in color with gloss Finish

- Poured polyurethane seamless gasket provides watertight, dust-tight environmental seal
- Multiple depths available in most sizes
- Flush sides for a perfect fit
- Multiple molded-in bosses for a variety of equipment mounting solutions
- Lift-off cover with 4 screws
- Tightening torque: M4-9 17 lb-in, M6 17-22 lb-in

## Listings

- UL/cUL File [UL File E64358]
- NEMA Ratings 1, 3R, 4, 4X, and 12
- IEC 60529 IP66 [UL File 362920]
- Flammability Rating: UL94-V2
- Non-flame propagating
- UV Exposure Rating: UL-f1
- Temperature Range: -40°F to 212°F [-40°C to 100°C]
- Certifications: cULus, REACH, CE, IEC



# BantamBox Series Polycarbonate Enclosures

## NEMA 1, 3R, 4, 4X and 12 with Screw Cover



| Bantam Box Series Polycarbonate Enclosures                                          |          |                             |          |                                      |                          |                     |
|-------------------------------------------------------------------------------------|----------|-----------------------------|----------|--------------------------------------|--------------------------|---------------------|
| Opaque Cover                                                                        | Price    | Clear Cover                 | Price    | Enclosure Overall Size HxWxD         | Subpanel                 | Drawing Link        |
| <a href="#">BB060555W</a>                                                           | \$34.50  | <a href="#">BBCC060555W</a> | \$35.00  | 2.56 x 1.97 x 2.17 [65 x 50 x 55]    | —                        | <a href="#">PDF</a> |
| <a href="#">BB080805W</a>                                                           | \$40.00  | <a href="#">BBCC080805W</a> | \$42.50  | 3.23 x 3.15 x 2.17 [82 x 80 x 55]    | <a href="#">BPB0808P</a> | <a href="#">PDF</a> |
| <a href="#">BB080809W</a>                                                           | \$45.50  | —                           | —        | 3.23 x 3.15 x 3.35 [82 x 80 x 85]    | <a href="#">BPB0808P</a> | <a href="#">PDF</a> |
| <a href="#">BB080810W</a>                                                           | \$46.00  | —                           | —        | 3.23 x 3.15 x 3.74 [82 x 80 x 95]    | <a href="#">BPB0808P</a> | <a href="#">PDF</a> |
| <a href="#">BB090603W</a>                                                           | \$38.50  | <a href="#">BBCC090603W</a> | \$42.00  | 3.86 x 2.52 x 1.46 [98 x 64 x 37]    | —                        | <a href="#">PDF</a> |
| <a href="#">BB128055W</a>                                                           | \$44.00  | <a href="#">BBCC128055W</a> | \$47.00  | 4.72 x 3.15 x 2.17 [120 x 80 x 55]   | <a href="#">BPB1280P</a> | <a href="#">PDF</a> |
| <a href="#">BBR128080W</a>                                                          | \$48.00  | —                           | —        | 4.72 x 3.15 x 3.15 [120 x 80 x 80]   | <a href="#">BPB1280P</a> | <a href="#">PDF</a> |
| <a href="#">BB128010W</a>                                                           | \$51.00  | —                           | —        | 4.72 x 3.15 x 3.94 [120 x 80 x 100]  | <a href="#">BPB1280P</a> | <a href="#">PDF</a> |
| <a href="#">BB121255W</a>                                                           | \$51.00  | —                           | —        | 4.80 x 4.72 x 2.17 [122 x 120 x 55]  | <a href="#">BPB1212P</a> | <a href="#">PDF</a> |
| <a href="#">BB121275W</a>                                                           | \$55.00  | <a href="#">BBCC121275W</a> | \$59.00  | 4.80 x 4.72 x 2.95 [122 x 120 x 75]  | <a href="#">BPB1212P</a> | <a href="#">PDF</a> |
| <a href="#">BB121211W</a>                                                           | \$64.00  | <a href="#">BBCC121211W</a> | \$68.00  | 4.80 x 4.72 x 4.13 [122 x 120 x 105] | <a href="#">BPB1212P</a> | <a href="#">PDF</a> |
| <a href="#">BB168055W</a>                                                           | \$53.00  | —                           | —        | 6.30 x 3.15 x 2.17 [160 x 80 x 55]   | <a href="#">BPB1680P</a> | <a href="#">PDF</a> |
| <a href="#">BB168090W</a>                                                           | \$58.00  | <a href="#">BBCC168090W</a> | \$61.00  | 6.30 x 3.15 x 3.54 [160 x 80 x 90]   | <a href="#">BPB1680P</a> | <a href="#">PDF</a> |
| <a href="#">BB161255W</a>                                                           | \$69.00  | <a href="#">BBCC161255W</a> | \$73.00  | 6.30 x 4.72 x 2.17 [160 x 120 x 55]  | <a href="#">BPB1612P</a> | <a href="#">PDF</a> |
| <a href="#">BB161290W</a>                                                           | \$71.00  | <a href="#">BBCC161290W</a> | \$75.00  | 6.30 x 4.72 x 3.54 [160 x 120 x 90]  | <a href="#">BPB1612P</a> | <a href="#">PDF</a> |
| <a href="#">BB161214W</a>                                                           | \$84.00  | <a href="#">BBCC161214W</a> | \$88.00  | 6.30 x 4.72 x 5.51 [160 x 120 x 140] | <a href="#">BPB1612P</a> | <a href="#">PDF</a> |
| <a href="#">BB201275W</a>                                                           | \$74.00  | <a href="#">BBCC201275W</a> | \$77.00  | 7.87 x 4.72 x 2.95 [200 x 120 x 75]  | <a href="#">BPB2012P</a> | <a href="#">PDF</a> |
| <a href="#">BB201290W</a>                                                           | \$75.00  | —                           | —        | 7.87 x 4.72 x 3.54 [200 x 120 x 90]  | <a href="#">BPB2012P</a> | <a href="#">PDF</a> |
| <a href="#">BB201510W</a>                                                           | \$86.00  | <a href="#">BBCC201510W</a> | \$92.00  | 7.87 x 5.91 x 3.94 [200 x 150 x 100] | <a href="#">BPB2015P</a> | <a href="#">PDF</a> |
| <a href="#">BB201513W</a>                                                           | \$89.00  | <a href="#">BBCC201513W</a> | \$96.00  | 7.87 x 5.91 x 4.92 [200 x 150 x 125] | <a href="#">BPB2015P</a> | <a href="#">PDF</a> |
| <a href="#">BB251690W</a>                                                           | \$89.00  | —                           | —        | 9.84 x 6.30 x 3.54 [250 x 160 x 90]  | <a href="#">BPB2516P</a> | <a href="#">PDF</a> |
| <a href="#">BB251611W</a>                                                           | \$106.00 | —                           | —        | 9.84 x 6.30 x 4.53 [250 x 160 x 115] | <a href="#">BPB2516P</a> | <a href="#">PDF</a> |
| <a href="#">BB251612W</a>                                                           | \$108.00 | <a href="#">BBCC251612W</a> | \$114.00 | 9.84 x 6.30 x 4.72 [250 x 160 x 120] | <a href="#">BPB2516P</a> | <a href="#">PDF</a> |
| <a href="#">BB251615W</a>                                                           | \$110.00 | <a href="#">BBCC251615W</a> | \$118.00 | 9.84 x 6.30 x 5.91 [250 x 160 x 150] | <a href="#">BPB2516P</a> | <a href="#">PDF</a> |
| Notes: Subpanels must be ordered separately.<br>Dimensions in inches [millimeters]. |          |                             |          |                                      |                          |                     |

# Subpanels for BantamBox Series Enclosures



## Phenolic Resin Hard Paper Subpanels

Lightweight, durable and electrically resistant. Includes mounting hardware.



**BPB0808P**

| BantamBox Series Subpanels                |         |                         |
|-------------------------------------------|---------|-------------------------|
| Part Number                               | Price   | Subpanel Size           |
| <b><u>BPB0808P</u></b>                    | \$5.25  | 2.83 x 2.76 [72 x 70]   |
| <b><u>BPB1280P</u></b>                    | \$5.25  | 4.33 x 2.76 [110 x 70]  |
| <b><u>BPB1680P</u></b>                    | \$6.25  | 5.91 x 2.76 [150 x 70]  |
| <b><u>BPB1212P</u></b>                    | \$8.00  | 4.41 x 4.33 [112 x 110] |
| <b><u>BPB1612P</u></b>                    | \$8.25  | 5.94 x 4.41 [151 x 112] |
| <b><u>BPB2012P</u></b>                    | \$7.50  | 7.44 x 4.29 [189 x 109] |
| <b><u>BPB2015P</u></b>                    | \$10.50 | 7.52 x 5.59 [191 x 142] |
| <b><u>BPB2516P</u></b>                    | \$12.50 | 9.53 x 5.98 [242 x 152] |
| Note: Dimensions in inches [millimeters]. |         |                         |