

BantamBox Series Polycarbonate Enclosures

NEMA 1, 3R, 4, 4X and 12 with Screw Cover



BB060555W



BBCC090603W

Applications

BantamBox offers an all-polycarbonate product with clear or opaque covers. These enclosures include an external flush wall design, unobstructed internal sidewalls, 304 stainless steel cover screws, and watertight seal.

Construction

- Polycarbonate for 1480 in-lb, high impact resistance per UL746C

Gray in color with gloss Finish

- Poured polyurethane seamless gasket provides watertight, dust-tight environmental seal
- Multiple depths available in most sizes
- Flush sides for a perfect fit
- Multiple molded-in bosses for a variety of equipment mounting solutions
- Lift-off cover with 4 screws
- Tightening torque: M4-9 17 lb-in, M6 17-22 lb-in

Listings

- UL/cUL File [UL File E64358]
- NEMA Ratings 1, 3R, 4, 4X, and 12
- IEC 60529 IP66 [UL File 362920]
- Flammability Rating: UL94-V2
- Non-flame propagating
- UV Exposure Rating: UL-f1
- Temperature Range: -40°F to 212°F [-40°C to 100°C]
- Certifications: cULus, REACH, CE, IEC



BantamBox Series Polycarbonate Enclosures

NEMA 1, 3R, 4, 4X and 12 with Screw Cover



Bantam Box Series Polycarbonate Enclosures						
Opaque Cover	Price	Clear Cover	Price	Enclosure Overall Size HxWxD	Subpanel	Drawing Link
BB060555W	\$34.50	BBCC060555W	\$35.00	2.56 x 1.97 x 2.17 [65 x 50 x 55]	—	PDF
BB080805W	\$40.00	BBCC080805W	\$42.50	3.23 x 3.15 x 2.17 [82 x 80 x 55]	BPB0808P	PDF
BB080809W	\$45.50	—	—	3.23 x 3.15 x 3.35 [82 x 80 x 85]	BPB0808P	PDF
BB080810W	\$46.00	—	—	3.23 x 3.15 x 3.74 [82 x 80 x 95]	BPB0808P	PDF
BB090603W	\$38.50	BBCC090603W	\$42.00	3.86 x 2.52 x 1.46 [98 x 64 x 37]	—	PDF
BB128055W	\$44.00	BBCC128055W	\$47.00	4.72 x 3.15 x 2.17 [120 x 80 x 55]	BPB1280P	PDF
BBR128080W	\$48.00	—	—	4.72 x 3.15 x 3.15 [120 x 80 x 80]	BPB1280P	PDF
BB128010W	\$51.00	—	—	4.72 x 3.15 x 3.94 [120 x 80 x 100]	BPB1280P	PDF
BB121255W	\$51.00	—	—	4.80 x 4.72 x 2.17 [122 x 120 x 55]	BPB1212P	PDF
BB121275W	\$55.00	BBCC121275W	\$59.00	4.80 x 4.72 x 2.95 [122 x 120 x 75]	BPB1212P	PDF
BB121211W	\$64.00	BBCC121211W	\$68.00	4.80 x 4.72 x 4.13 [122 x 120 x 105]	BPB1212P	PDF
BB168055W	\$53.00	—	—	6.30 x 3.15 x 2.17 [160 x 80 x 55]	BPB1680P	PDF
BB168090W	\$58.00	BBCC168090W	\$61.00	6.30 x 3.15 x 3.54 [160 x 80 x 90]	BPB1680P	PDF
BB161255W	\$69.00	BBCC161255W	\$73.00	6.30 x 4.72 x 2.17 [160 x 120 x 55]	BPB1612P	PDF
BB161290W	\$71.00	BBCC161290W	\$75.00	6.30 x 4.72 x 3.54 [160 x 120 x 90]	BPB1612P	PDF
BB161214W	\$84.00	BBCC161214W	\$88.00	6.30 x 4.72 x 5.51 [160 x 120 x 140]	BPB1612P	PDF
BB201275W	\$74.00	BBCC201275W	\$77.00	7.87 x 4.72 x 2.95 [200 x 120 x 75]	BPB2012P	PDF
BB201290W	\$75.00	—	—	7.87 x 4.72 x 3.54 [200 x 120 x 90]	BPB2012P	PDF
BB201510W	\$86.00	BBCC201510W	\$92.00	7.87 x 5.91 x 3.94 [200 x 150 x 100]	BPB2015P	PDF
BB201513W	\$89.00	BBCC201513W	\$96.00	7.87 x 5.91 x 4.92 [200 x 150 x 125]	BPB2015P	PDF
BB251690W	\$89.00	—	—	9.84 x 6.30 x 3.54 [250 x 160 x 90]	BPB2516P	PDF
BB251611W	\$106.00	—	—	9.84 x 6.30 x 4.53 [250 x 160 x 115]	BPB2516P	PDF
BB251612W	\$108.00	BBCC251612W	\$114.00	9.84 x 6.30 x 4.72 [250 x 160 x 120]	BPB2516P	PDF
BB251615W	\$110.00	BBCC251615W	\$118.00	9.84 x 6.30 x 5.91 [250 x 160 x 150]	BPB2516P	PDF
Notes: Subpanels must be ordered separately. Dimensions in inches [millimeters].						

Subpanels for BantamBox Series Enclosures



Phenolic Resin Hard Paper Subpanels

Lightweight, durable and electrically resistant. Includes mounting hardware.



[BPB0808P](#)

BantamBox Series Subpanels		
Part Number	Price	Subpanel Size
<u>BPB0808P</u>	\$5.25	2.83 x 2.76 [72 x 70]
<u>BPB1280P</u>	\$5.25	4.33 x 2.76 [110 x 70]
<u>BPB1680P</u>	\$6.25	5.91 x 2.76 [150 x 70]
<u>BPB1212P</u>	\$8.00	4.41 x 4.33 [112 x 110]
<u>BPB1612P</u>	\$8.25	5.94 x 4.41 [151 x 112]
<u>BPB2012P</u>	\$7.50	7.44 x 4.29 [189 x 109]
<u>BPB2015P</u>	\$10.50	7.52 x 5.59 [191 x 142]
<u>BPB2516P</u>	\$12.50	9.53 x 5.98 [242 x 152]
Note: Dimensions in inches [millimeters].		