

CAPTRON

CANEO Series10 Standard Capacitive Switches

**IO-Link****CS10KMLDT-C12-00AE****CS10KMLDT-C20-00BB****CS10KMLDT-B14-054A**

*22mm Series10 Standard Capacitive Switches

Part Number	Price	LED Color (Idle/Active)	Switch Type	LED Control	Legend	Symbol Illuminated	Connection	Output Pulse	Drawing Link		
CS10KMLDT-C10-00A6	\$59.00	green/red	Dynamic	Semi-automatic	START	No	4-pole	Approx. 300ms	PDF		
CS10KMLDT-C10-00A7	\$59.00		Static					Continuous when actuated	PDF		
CS10KMLDT-C11-0543	\$59.00	red/green	Dynamic		STOP			Approx. 300ms	PDF		
CS10KMLDT-C11-0547	\$59.00		Static					Continuous when actuated	PDF		
CS10KMLDT-C12-00AE	\$59.00	green/red	Dynamic		ON/OFF			Approx. 300ms	PDF		
CS10KMLDT-C12-00AF	\$59.00		Static					Continuous when actuated	PDF		
CS10KMLDT-C12-00B0	\$59.00		Toggle					Toggle	PDF		
CS10KMLDT-C16-0548	\$59.00	red/green	Static		Power Symbol				Continuous when actuated	PDF	
CS10KMLDT-C16-0549	\$59.00	green/red								Dynamic	START
CS10KMLDT-C17-00B7	\$59.00		Static		Continuous when actuated			PDF			
CS10KMLDT-C20-00BB	\$59.00		Dynamic		Manual			-	5-pole	Approx. 300ms	PDF
CS10KMLDT-C20-00BC	\$59.00						Static				Semi-automatic
CS10KMLDT-C20-00BD	\$59.00		Dynamic	Manual	5-pole			Continuous when actuated	PDF		
CS10KMLDT-C20-00BE	\$59.00						red/green		Dynamic	Semi-automaticSemi-automatic	START
CS10KMLDT-B10-00C7	\$59.00		Static	Continuous when actuated	PDF						
CS10KMLDT-B10-00C8	\$59.00		red/green	Dynamic	STOP	Approx. 300ms	PDF				
CS10KMLDT-B11-00C9	\$59.00			Static		Continuous when actuated	PDF				
CS10KMLDT-B11-00CA	\$59.00		green/red		Power Symbol			Continuous when actuated	PDF		
CS10KMLDT-B14-054A	\$59.00		red/green	PDF							
CS10KMLDT-B14-054B	\$59.00			PDF							

*Purchase cable separately.

22mm Series10 Standard Capacitive Switches

Part Number	Price	LED Color (Idle/Active)	Switch Type	LED Control	Legend	Symbol Illuminated	Connection	Output Pulse	Drawing Link
<u>CS10KMMDU-B13-092D</u>	\$59.00	blue/off	dynamic	automatic	RESET	Yes	7.87in (200mm) pigtail	Approx. 300ms	<u>PDF</u>
<u>CS10KMMDU-B14-0A5F</u>	\$59.00	green/red	static	semi-automatic	Power Symbol	No		Continuous when actuated	<u>PDF</u>
<u>CS10KMMDU-C20-0793</u>	\$59.00		dynamic		-	Yes		Approx. 300ms	<u>PDF</u>

Note: An additional pigtail connection makes these part numbers distinguishable from other parts in this series.



CANEO Series10 Standard Capacitive Switches


22mm Series10 Standard Capacitive Switches Specifications	
Supply Voltage	24VDC [8.4 to 32V]
Output	PNP-N.O.
Load Current	Max 200mA
Current Consumption	Max 40mA @24V
Operating Temperature	-30 to 65°C [-22 to 149°F]
Storage Temperature	-30 to 65°C [-22 to 149°F]
IP Rating	IP69K
Material	Housing: Polycarbonate (PC) Switch surface: Polycarbonate (PC)
Weight (lbs)	0.1
Agency Approvals	CE, CSA




IO-Link Specifications	
IO-Link	v1.1
Port Speed	COM2
SIO Supported	Yes
ISDU Supported	Yes
Data Storage	Yes
Block Parameter	No

Wiring Diagrams


Plug M12, 4-pin




Plug M12, 5-pin



4-pin



5-pin



Safety

General safety

All work on electrical systems or operating equipment may only be carried out by a specially qualified electrician according to the applicable electrotechnical regulations.

The safety of the system in which the SENSORswitch is integrated is the responsibility of the operator.



WARNING

Improper work on electrical systems!

Electric shock can result in death or life-threatening injuries.

- ▶ Before working on electrical systems, disconnect them from their voltage supply and secure them against being switched on again.
- ▶ Wear appropriate personal protective equipment (PPE).




CANEO Series10 Hygienic Capacitive Switches

Overview

MEETS THE HIGHEST OF HYGIENE STANDARDS AS THE FIRST EHEDG-CERTIFIED SWITCH

The CANEO Series10 Hygienic is the first EHEDG-certified switch (European Hygienic Engineering and Design Group). It also meets FDA requirements, making it perfect for all industries with high requirements for hygienic cleaning, such as the food & beverages and medicine & pharmaceuticals sectors.



CS10HMSDT-C20-030B

CS10HMSDT-B14-0475

*22mm Series10 Hygienic Capacitive Switches									
Part Number	Price	LED Color (Idle/Active)	Switch Type	LED Control	Legend	Symbol Illuminated	Connection (M12)	Output Pulse	Drawing Link
CS10HMSDT-C10-02F1	\$79.00	green/red	Dynamic	Semi-automatic	START	No	4-pole	Approx. 300ms	PDF
CS10HMSDT-C10-02F2	\$79.00		Static					Continuous when actuated	PDF
CS10HMSDT-C11-054C	\$79.00	red/green	Dynamic		STOP			Approx. 300ms	PDF
CS10HMSDT-C11-054D	\$79.00		Static					Continuous when actuated	PDF
CS10HMSDT-C12-02F9	\$79.00	green/red	Dynamic		ON/OFF			Approx. 300ms	PDF
CS10HMSDT-C12-02FA	\$79.00		Static					Continuous when actuated	PDF
CS10HMSDT-C12-02FB	\$79.00		Toggle					Toggle	PDF
CS10HMSDT-C16-0469	\$79.00	red/green	Static		Power Symbol			Continuous when actuated	PDF
CS10HMSDT-C16-054E	\$79.00								PDF
CS10HMSDT-C17-0306	\$79.00	green/red	Dynamic		START			Approx. 300ms	PDF
CS10HMSDT-C17-0307	\$79.00		Static					Continuous when actuated	PDF
CS10HMSDT-C17-030A	\$79.00		Dynamic	Manual	5-pole		Approx. 300ms	PDF	
CS10HMSDT-C20-030B	\$79.00		Static	Semi-automatic			4-pole	Continuous when actuated	PDF
CS10HMSDT-C20-020C	\$79.00			Manual				5-pole	PDF
CS10HMSDT-B10-0314	\$79.00		Dynamic	Semi-automatic	START	Yes	4-pole	Approx. 300ms	PDF
CS10HMSDT-B10-0315	\$79.00	Static	Continuous when actuated					PDF	
CS10HMSDT-B11-0316	\$79.00	red/green	Dynamic		STOP			Approx. 300ms	PDF
CS10HMSDT-B11-0473	\$79.00		Static					Continuous when actuated	PDF
CS10HMSDT-B14-0475	\$79.00	green/red						Power Symbol	

22mm Series10 Hygienic Capacitive Switches									
Part Number	Price	LED Color (Idle/Active)	Switch Type	LED Control	Legend	Symbol Illuminated	Connection	Output Pulse	Drawing Link
CS10HMODU-C16-0A60	\$79.00	green/red	Static	Semi-automatic	Power Symbol	Yes	7.87in (200mm) pigtail	Continuous when actuated	PDF
CS10HMODU-C19-0A3F	\$79.00	teal/red		Automatic	RESET	No			PDF
CS10HMODU-C20-0A61	\$79.00	green/red		Semi-automatic	-				PDF

Note: An additional pigtail connection makes these part numbers distinguishable from other parts in this series.



CANEO Series10 Hygienic Capacitive Switches


22mm Series10 Hygienic Capacitive Switches Specifications	
Supply Voltage	24VDC [8.4 to 32V]
Output	PNP-N.O.
Load Current	Max 200mA
Current Consumption	Max 40mA @24V
Operating Temperature	-30 to 65°C [-22 to 149°F]
Storage Temperature	-30 to 65°C [-22 to 149°F]
IP Rating	IP69K
Material	Housing: Stainless Steel (V4A) Switch surface: Polycarbonate (PC)
Weight (lbs)	0.1
Agency Approvals	CE, CSA




IO-Link Specifications	
IO-Link	v1.1
Port Speed	COM2
SIO Supported	Yes
ISDU Supported	Yes
Data Storage	Yes
Block Parameter	No

Wiring Diagrams


Plug M12, 4-pin




Plug M12, 5-pin



4-pin



5-pin



WARNING



Improper work on electrical systems!

Electric shock can result in death or life-threatening injuries.

- Before working on electrical systems, disconnect them from their voltage supply and secure them against being switched on again.
- Work on electrical installations should be carried out only by qualified personnel in compliance with local and national electrical regulations and specifications.

Intended use

The SENSORswitch is intended for use in accordance with the items listed here, the values from the "Technical specifications" chapter and the product description.

CAPTRON

CANEO Series10 Stainless Steel Capacitive Switches

**IO-Link****CS10SMTDT-C12-044C****CS10SMTDT-C20-0453****CS10SMTDT-B14-045E*****22mm Series10 Stainless Steel Capacitive Switches**

Part Number	Price	LED Color (Idle/Active)	Switch Type	LED Control	Legend	Symbol Illuminated	Connection (M12)/	Output Pulse	Drawing Link		
CS10SMTDT-C10-0448	\$73.00	green/red	Dynamic	Semi-automatic	START	No	4-pole	Approx. 300ms	PDF		
CS10SMTDT-C10-0449	\$73.00		Static		STOP			Continuous when actuated	PDF		
CS10SMTDT-C11-054F	\$73.00	red/green	Dynamic					Approx. 300ms	PDF		
CS10SMTDT-C11-0550	\$73.00		Static		ON/OFF			Continuous when actuated	PDF		
CS10SMTDT-C12-044C	\$73.00	green/red	Dynamic					Approx. 300ms	PDF		
CS10SMTDT-C12-044D	\$73.00		Static					Continuous when actuated	PDF		
CS10SMTDT-C12-044E	\$73.00		Toggle		Power Symbol			Toggle	PDF		
CS10SMTDT-C16-044F	\$73.00	red/green	Static					Continuous when actuated	PDF		
CS10SMTDT-C16-0551	\$73.00		Dynamic		START			Approx. 300ms	PDF		
CS10SMTDT-C17-0451	\$73.00	green/red	Static					Continuous when actuated	PDF		
CS10SMTDT-C17-0452	\$73.00		Dynamic	-			5-pole	Approx. 300ms	PDF		
CS10SMTDT-C20-0453	\$73.00		Dynamic					Manual	4-pole	Continuous when actuated	PDF
CS10SMTDT-C20-0454	\$73.00		Static				Semi-automatic	5-pole		Continuous when actuated	PDF
CS10SMTDT-C20-0455	\$73.00						Manual		START		4-pole
CS10SMTDT-C20-0456	\$73.00		Dynamic	STOP			Yes	Continuous when actuated			
CS10SMTDT-B10-0457	\$73.00		red/green					Dynamic	Semi-automatic	Power Symbol	
CS10SMTDT-B10-0458	\$73.00	Static		Continuous when actuated	PDF						
CS10SMTDT-B11-045B	\$73.00	green/red	Static	Power Symbol	4-pole	Approx. 300ms		PDF			
CS10SMTDT-B11-045C	\$73.00					Continuous when actuated		PDF			
CS10SMTDT-B14-045E	\$73.00	red/green	Static			Power Symbol	4-pole	Continuous when actuated		PDF	
CS10SMTDT-B14-0460	\$73.00							red/green	Continuous when actuated	PDF	

*Purchase cable separately.



CANEO Series10 Stainless Steel Capacitive Switches

22mm Series10 Stainless Steel Capacitive Switches Specifications

Supply Voltage	24VDC [8.4 to 32V]
Output	PNP-N.O.
Load Current	Max 200mA
Current Consumption	Max 40mA @24V
Operating Temperature	-30 to 65°C [-22 to 149°F]
Storage Temperature	-30 to 65°C [-22 to 149°F]
IP Rating	IP69K
Material	Housing: Stainless Steel (V4A) Switch surface: Polycarbonate (PC)
Weight (lbs)	0.1
Agency Approvals	CE, CSA




IO-Link Specifications


IO-Link	v1.1
Port Speed	COM2
SIO Supported	Yes
ISDU Supported	Yes
Data Storage	Yes
Block Parameter	No

Wiring Diagrams


Plug M12, 4-pin




Plug M12, 5-pin



4-pin



5-pin





CANEO Series41 and Series40 Standard Capacitive Switches



IO-Link

[CS41KCRBK-P10-01E7](#)

[CS41KCRBK-P11-029F](#)

[CS41KCRBK-P20-0253](#)

*22mm Series41 and Series40 Standard Capacitive Switches											
Part Number	Price	LED Color (Idle/Active)	Switch Type	LED Control	Legend	Symbol Illuminated	Connection	Output Pulse	Drawing Link		
CS40KMSBN-P20-063A	\$159.00	green/red	Dynamic	Automatic	-	No	3-pole	Approx. 300ms	PDF		
CS40KMSBN-P10-05BC	\$159.00			Semi-automatic	Hand Symbol				-	4-pole	PDF
CS41KCRBK-P10-01E7	\$142.00			Automatic							PDF
CS41KCRBK-P10-029A	\$142.00			Semi-automatic			PDF				
CS41KCRBK-P10-029B	\$142.00			Manual	5-pole		PDF				
CS41KCRBK-P11-029F	\$142.00			Automatic	4-pole		PDF				
CS41KCRBK-P11-02A0	\$142.00			Semi-automatic	4-pole		PDF				
CS41KCRBK-P11-02A1	\$142.00			Manual	5-pole		PDF				
CS41KDMBL-P11-0552	\$142.00			Automatic	3-pole		PDF				
CS41KDMBL-P11-0553	\$142.00	Semi-automatic		4-pole	PDF						
CS41KDMBL-P11-0554	\$142.00	Manual		5-pole	PDF						
CS41KDMBL-P12-0555	\$142.00	Automatic		3-pole	PDF						
CS41KDMBL-P12-0556	\$142.00	Semi-automatic		4-pole	PDF						
CS41KDMBL-P12-0557	\$142.00	Manual		5-pole	PDF						
CS41KCRBK-P13-02AB	\$142.00	green/red		Automatic	START		3-pole		PDF		
CS41KDMBL-P13-0591	\$142.00			Semi-automatic			4-pole		PDF		
CS41KDMBL-P13-0594	\$142.00			Manual			5-pole		PDF		
CS41KCRBK-P20-0253	\$142.00			Automatic	-		3-pole		PDF		
CS41KDMBL-P20-0595	\$142.00		Semi-automatic	4-pole		PDF					
CS41KDMBL-P20-0596	\$142.00		Manual	5-pole		PDF					

*Purchase cable separately.



CANEO Series41 Standard Capacitive Switches




22mm Series41 Standard Capacitive Switches Specifications	
Supply Voltage	24VDC [19.2 to 28.8 V]
Output	PNP-N.O.
Load Current	Max 200mA
Current Consumption	Max 90mA @24V
Operating Temperature	-25 to 50°C [-13 to 122°F]
Storage Temperature	-25 to 50°C [-13 to 122°F]
IP Rating	IP69K
Material	Housing : Polycarbonate (PC) Switch surface Polycarbonate (PC)
Weight (lbs)	0.1
Agency Approvals	CE, CSA


IO-Link Specifications	
IO-Link	v1.1
Port Speed	COM2
SIO Supported	Yes
ISDU Supported	Yes
Data Storage	Yes
Block Parameter	No

Wiring Diagrams


Plug M12, 3-pin




Plug M12, 4-pin




Plug M12, 5-pin




3-pin



4-pin



5-pin



CAPTRON

CANEO Series41 and Series40 Standard Display Capacitive Switches

**CD41KCRBK-P20-0254**

*Series41 and Series40 Standard Display Capacitive Switches


Part Number	Price	LED Color (Idle/Active)	Switch Type	LED Control	Legend	Symbol Illuminated	Output Pulse	Connection	Agency Approvals	Weight (lbs)	Drawing Link
CD40KMSBN-P20-050F	\$175.00	teal/red	Static	Automatic	-	No	Continuous when actuated	3-pole	CE, CSA	0.25	PDF
CD41AARBK-P20-0256	\$254.00	green/red	Dynamic				Approx 300ms				PDF
CD41KCRBK-P20-0254	\$171.00			4-pole				PDF			
CD41KCRBK-P20-0597	\$171.00						5-pole	PDF			
CD41KCRBK-P20-0598	\$171.00			PDF							

Series41 Standard Display Capacitive Switches Specifications


Supply Voltage	Output	Output Pulse	Load Current	Current Consumption	Operating Temperature	Storage Temperature	IP Rating	Material
24VDC [19.2 to 28.8 V]	PNP - N.O.	Approx. 300ms	Max 200mA	Max 90mA @24V	-25 to 50°C [-13 to 122°F]	-25 to 50°C [-13 to 122°F]	IP69K	Housing: Polycarbonate [PC] Switch surface: Polycarbonate [PC]

Wiring Diagrams


Plug M12, 3-pin



Plug M12, 4-pin




Plug M12, 5-pin




IO-Link Specifications

IO-Link	v1.1
Port Speed	COM2
SIO Supported	Yes
ISDU Supported	Yes
Data Storage	Yes
Block Parameter	No

3-pin



4-pin



5-pin

