



Pliers & Cutting Tools




Diagonal Cutting Pliers

CHANNELLOCK® high leverage diagonal cutting pliers feature Xtreme Leverage Technology (XLT™) which makes cutting easier than ever. By positioning the rivet closer to the cutting edge, considerably less force is required to cut than other high leverage designs. State-of-the-art laser heat treating offers a strong and consistent pattern across the cutting edge for increased strength and longevity. These pliers also offer a slimmer, lighter, and better-balanced design for maximum performance and accessibility. CHANNELLOCK diagonal cutting pliers are made in the USA and forged from high carbon U.S. steel that is specially coated for ultimate rust prevention.

Features

- Xtreme Leverage Technology (XLT™) increases performance and reduces hand fatigue
- Laser heat-treated cutting edges perform better and last longer
- Precision-machined knife and anvil style cutting edges ensure perfect mating for superior performance and longevity
- CHANNELLOCK BLUE® grips for comfort



Diagonal Cutting Pliers								
Part Number	Part Image	Pliers Type	Overall Length	Jaw Length	Jaw Thickness	Jaw Width	Price	
<u>337</u>		Diagonal	7.2in (184mm)	0.88in (22.3mm)	0.45in (11.4mm)	N/A	\$25.00	
<u>447</u>		Curved Diagonal	7.7in (196mm)	1.02in (25.9mm)	0.49in (12.4mm)	1.06in (26.9mm)	\$33.00	
<u>449</u>		Curved Diagonal	9.5in (241mm)	1.02in (25.9mm)	0.49in (12.4mm)	1.12in (28.4mm)	\$34.00	



Diagonal

[337](#)



Curved Diagonal

[447](#)

[449](#)