



# Pliers & Cutting Tools

## Tongue and Groove Pliers

CHANNELLOCK® straight jaw tongue and groove pliers are built to last with a PERMALOCK® fastener to eliminate nut and bolt failure, a patented reinforcing edge to minimize stress breakage, and laser-hardened teeth to provide a better, longer lasting grip. CHANNELLOCK straight jaw tongue and groove pliers are made in USA and forged from high-carbon U.S. steel that is specially coated for ultimate rust prevention.

### Features

- Tongue and groove pliers provide a strong, versatile grip for use in both directions
- Reliable PERMALOCK fastener eliminates nut and bolt failure with increased joint strength
- Strong 90-degree, laser-hardened teeth for superior grip and longevity
- Undercut tongue and groove won't slip
- CHANNELLOCK BLUE® grips for added comfort and reduced hand fatigue



Tongue and Groove Pliers						
Part Number	Part Image	Overall Length	Jaw Length	Jaw Capacity	Jaw Thickness	Price
<a href="#"><u>426</u></a>		6.5in (165mm)	0.81in (20.6mm)	0.87in (22.1mm)	0.47in (11.9mm)	\$15.00
<a href="#"><u>420</u></a>		9.5in (241mm)	1.12in (28.4mm)	1.50in (38.1mm)	0.47in (11.9mm)	\$18.00
<a href="#"><u>430</u></a>		10.0in (254mm)	1.38in (35.1mm)	2.00in (50.8mm)	0.44in (11.2mm)	\$19.00
<a href="#"><u>440</u></a>		12.0in (305mm)	1.50in (38.1mm)	2.25in (57.2mm)	0.50in (12.7mm)	\$21.00
<a href="#"><u>460</u></a>		16.5in (418mm)	2.56in (65.0mm)	3.75in (95.3mm)	0.59in (15.0mm)	\$36.00