

Comepi Safety Solenoid Locking Switches with Unique RFID Coding



Comepi's uniquely coded RFID guard locking safety switch is an electromagnetic device with a separate RFID actuator.

This RFID coded version guarantees protection against easy bypass of the device.

The solenoid can be used to lock the actuator in place to prevent access to the protected area.

Features

- Single RFID coded tongue (key) prevents unauthorized bypass
- The AFEPMK series allows for replacement keys to be retaught
- Power to lock units
- Separate circuits to monitor the guard closed and solenoid



[AFEPMKR1FR3-024E](#)

RFID Coded Safety Solenoid Locking Switch Selection Guide

Part Number	Price	Locking Mode	Actuator Type	Head Position	Holding Force	Safety Output Type	Monitoring Output Type	IP Rating	Drawing
AFEPMKR1FR3-024E	\$296.00	24 VDC to lock	Unique RFID	0-degree fixed	1200N	(2) N.C.	(1) N.C.	IP65	PDF
AFEPMKR2FR3-024E	\$296.00	24 VDC to lock	Unique RFID	90-degree fixed	1200N	(2) N.C.	(1) N.C.	IP65	PDF
AFEPMKR3FR3-024E	\$296.00	24 VDC to lock	Unique RFID	180-degree fixed	1200N	(2) N.C.	(1) N.C.	IP65	PDF
AFEPMKR4FR3-024E	\$296.00	24 VDC to lock	Unique RFID	270-degree fixed	1200N	(2) N.C.	(1) N.C.	IP65	PDF

RFID Coded Safety Solenoid Locking Switch Key Selection Guide

Part Number	Price	RFID	Hole Spacing	Material	Fits	Drawing
KEY29R	\$16.00	Uniquely coded	40mm	316 stainless steel	Comepi AFEPMK series safety switches	PDF



[KEY29R](#)


Comepi Safety Solenoid Locking Switches with Unique RFID Coding



AFEPMK Locking Switches with Unique RFID Coding Specifications		
Environmental		
Degree of Protection	IP65	
Operating Temperature Range	-20° to 55°C [-4° to 131°F]	
Storage Temperature Range	-30° to 80°C [-22° to 176°F]	
Rated Insulation Voltage	250V	
Pollution Degree	Degree 3	
Mechanical		
Mechanical Life	1,000,000 operations	
B10d	2,000,000 operations	
Enclosure Material	Reinforced thermoplastic	
Manual Unlock	Screw release	
Electrical		
Voltage Range	21.6 to 26.4 VDC	
Maximum Current	0.5 A	
Electrical Ratings	AC15	24VAC @ 50/60 Hz = 2A
	DC13	24VDC = 2A
Maximum Switching Frequency	10 cycles per minute	
Terminals Marking	According to IEC 60947-5-1	
Cable Entry	M12 8-pin connection	
Connecting Wire Size	22 to 16 AWG (0.34 to 1.5 mm ²)	
Reference Standards	IEC 60947-5-1 EN 60947-5-1 EN ISO 14119	
Agency Approvals	cULus, CE	
Tools Needed		
Phillips screwdriver, #1 #2		

Connection Diagram:

Connection Colors




Pin View from Switch
M12 Male

M12 8-PIN MALE CONNECTOR				
Pin	292 Cable*	295 Cable*	Signal	Description
1	White	Brown	E1	Ground
2	Brown	White	E2/A1**	24 VDC+
3	Green	Blue	A2	N.C. Signal Output (from A1)
4	Yellow	Black	B1	Input for External Consense +24VDC
5	Gray	Gray	21	N.C. Safety Contact 1
6	Pink	Pink	22	N.C. Safety Contact 1
7	Blue	Violet	41	N.C. Safety Contact 2
8	Red	Orange	42	N.C. Safety Contact 2

Notes:

* AutomationDirect sells M12 8-pole cables with two different color patterns (7000-170x1-292xxxx and 7000-170x1-295xxxx).

** Terminals E2 and A1 have a factory-installed jumper.



Safety Products



Warning: Safety products sold by AutomationDirect are Safety components only. The purchaser/installer is solely responsible for the application of these components and ensuring all necessary steps have been taken to assure each application and use meets all performance and applicable safety requirements and/or local, national and/or international safety codes as required by the application. AutomationDirect cannot certify that our products, used solely or in conjunction with other AutomationDirect or other vendors' products, will assure safety for any application. Any person using or applying any products sold by AutomationDirect is responsible for learning the safety requirements for their individual application and applying them, and therefore assumes all risks, and accepts full and complete responsibility, for the selection and suitability of the product for their respective application.

AutomationDirect does not provide design or consulting services, and cannot advise whether any specific application or use of our products would ensure compliance with the safety requirements for any application.