

CT Series NEMA 3R Double-Door Hinge Cover



Applications

Designed as a housing for current and voltage transformers, recorders, meters, relays and/or for terminal instrumentation. Can also be used as a service or junction box.



Construction

- 12- or 14-gauge carbon steel
- Fully seam welded and ground smooth, with weep hole
- Drip shield
- Lift-off hinges, gasketed doors
- Supplied with non-locking "T" handle
- Meter seal provisions
- Mounting holes in back provided
- Supplied with studs in back of enclosure to support optional wood subpanel (available from Wiegmann)
- Uses WA8 handle

Finish

- ANSI 61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL Listed Type 3R [UL file E23553]



CT Series NEMA 3R Double-Door Hinge Cover

Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
CTDD362412	\$674.00	14/14	24.38 x 36.42 x 12.06 [619 x 925 x 306]
CTDD363612	\$924.00	12/12	36.37 x 36.46 x 12.08 [924 x 926 x 307]
CTDD424212	\$1,132.00		42.37 x 42.46 x 12.08 [1076 x 1078 x 307]
CTDD484816	\$1,335.00		48.37 x 48.46 x 16.08 [1229 x 1231 x 408]

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawings.

Dimensions

