

CT Series NEMA 3R Single-Door Hinge Cover Wall-Mount



Applications

Designed as a housing for transformers, recorders, meters, relays and/or for terminal instrumentation. Can also be used as a service or junction box.



Construction

- 12- or 14-gauge carbon steel
- Fully seam welded and ground smooth, with weep hole
- Drip shield
- Lift-off hinges, gasketed doors
- Supplied with non-locking 1/4 turn latch
- Meter seal provisions
- Mounting holes in back
- Supplied with studs in back of enclosure to support optional wood sub panel (available from Wiegmann)
- Uses N1C14 series latches

Finish

- ANSI-61 gray polyester powder light texture inside and out over phosphatized surfaces

Listings

- UL Listed Type 3R [UL file E23553]



Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1-10 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.

CT Series NEMA 3R Single-Door Hinge Cover

Part Number	Price	Body/Door Steel Gauge	Enclosure Size HxWxD
CTSD121810	Retired	14/14	18.38 x 12.38 x 10.06 [467 x 314 x 256]
CTSD182410	Retired		24.38 x 18.38 x 10.06 [619 x 467 x 256]
CTSD202010	Retired		20.38 x 20.38 x 10.06 [518 x 518 x 256]
CTSD202412	Retired		24.38 x 20.38 x 12.06 [619 x 518 x 306]
CTSD242412	Retired		24.38 x 24.38 x 12.06 [619 x 619 x 306]
CTSD243012	Retired		30.38 x 24.38 x 12.06 [772 x 619 x 306]
CTSD243612	Retired		36.38 x 24.38 x 12.06 [924 x 619 x 306]
CTSD303612	Retired	12/12	36.38 x 30.37 x 12.08 [924 x 771 x 307]

Notes: Dimensions in inches [millimeters]

Letters in table correspond to letters on dimensional drawings.

Dimensions

