



Wiring Accessories

Crimping Tools

Crimping Tools			
Part Number	Description	Weight	Price
<u>K70ZA000113</u>	Crimping tool for use with single ferrules AWG 20 - 10 [0.5 - 6 mm ²] and twin ferrules AWG 2 x 18 - 2 x 12 [2 x 0.75 - 2 x 4 mm ²]. 5 crimping positions. With and without insulating collar. Conforms to DIN 46228 part 1 and 2.	0.74 lb [335g]	\$115.00
<u>K70ZA000117</u>	Crimping tool for use with single ferrules AWG 10 - 4 [6 - 25 mm ²] and twin ferrules AWG 2 x 12 - 2 x 8 [2 x 4 - 2 x 10 mm ²]. 4 crimping positions. Conforms to DIN 46228 part 1 and 4.	1.19 lb [540g]	\$124.00
<u>K70ZA000130</u>	Crimping tool for PVC-insulated terminals AWG 20 - 10 [0.5 - 6 mm ²]. 3 crimping positions.	1.12 lb [510g]	\$115.00

Note: Z&F crimping tools recommended by the ferrule manufacturer before terminating in terminal blocks, wire connectors, or end-product terminals (such as starters, etc.).

[K70ZA000113](#)



[K70ZA000117](#)



[K70ZA000130](#)



Crimping Tools Cross Reference				
	Part Number		<u>K70ZA000113</u>	<u>K70ZA000117</u>
	Standard	DIN		
Single Ferrules	<u>V30AE000006</u>	<u>V30AE000038</u>	X	—
	<u>V30AE000009</u>	<u>V30AE000041</u>	X	—
	<u>V30AE000013</u>	<u>V30AE000045</u>	X	—
	<u>V30AE000016</u>	<u>V30AE000048</u>	X	—
	<u>V30AE000017</u>	<u>V30AE000049</u>	X	—
	<u>V30AE000052</u>	<u>V30AE000052</u>	X	—
	<u>V30AE000053</u>	<u>V30AE000053</u>	X	—
	<u>V30AE000055</u>	<u>V30AE000055</u>	X	—
	<u>V30AE000056</u>	<u>V30AE000056</u>	X	—
	<u>V30AE000025</u>	<u>V30AE000058</u>	X	X
	<u>V30AE000026</u>	<u>V30AE000059</u>	X	X
	<u>V30AE000027</u>	<u>V30AE000060</u>	—	X
	<u>V30AE000028</u>	<u>V30AE000061</u>	—	X
	<u>V30AE000029</u>	<u>V30AE000062</u>	—	X
	<u>V30AE000030</u>	<u>V30AE000063</u>	—	X
	<u>V30AE000031</u>	<u>V30AE000064</u>	—	X
	<u>V30AE000033</u>	<u>V30AE000067</u>	—	—
	<u>V30AE000035</u>	<u>V30AE000070</u>	—	—
Twin Ferrules	<u>V30AE001134</u>	<u>V30AE001145</u>	X	—
	<u>V30AE000606</u>	<u>V30AE000607</u>	X	—
	<u>V30AE000733</u>	<u>V30AE000734</u>	X	—
	<u>V30AE000608</u>	<u>V30AE000609</u>	X	—
	<u>V30AE000735</u>	<u>V30AE000736</u>	X	—
	<u>V30AE000623</u>	<u>V30AE000625</u>	X	—
	<u>V30AE000737</u>	<u>V30AE000738</u>	X	—
	<u>V30AE000611</u>	<u>V30AE000611</u>	X	—
	<u>V30AE000748</u>	<u>V30AE000748</u>	X	—
	<u>V30AE001148</u>	<u>V30AE001148</u>	X	X
	<u>V30AE001139</u>	<u>V30AE001150</u>	—	X
	<u>V30AE001141</u>	<u>V30AE001152</u>	—	X
	<u>V30AE001143</u>	<u>V30AE001154</u>	—	X

Wiring Accessories – Crimping Tools

Crimping Tools Overview

Our high-quality industrial crimping tools are designed to crimp a wide range of insulated and non-insulated crimping terminals, ferrules, and connectors. They feature ergonomic handles and controlled-cycle ratcheting mechanisms to guarantee a uniform crimp every time. Choose from fixed or interchangeable die tools or tool/die sets with multiple dies.

Interchangeable-Die Crimping Tools			
Part #	Description *	Qty	Price
<u>DN-CT-HDL</u>	Crimping tool handle for DN-CT-Dx dies (dies NOT included) Approximate dimensions: 9.75 x 2.52 x 0.95 in (234 x 64 x 24 mm); 16.2 oz (460g)	1	\$67.00
<u>DN-CT-D1</u>	Die set for DN-CT-HDL; 26-22 & 12-10 AWG (0.1-0.4 & 4-6 mm ²) green & yellow insulated terminals	1	\$73.00
<u>DN-CT-D2</u>	Die set for DN-CT-HDL; 22-14 AWG (0.5-2.5 mm ²) red & blue insulated terminals	1	\$73.00
<u>DN-CT-D3</u>	Die set for DN-CT-HDL; 22-10 AWG (0.5-6 mm ²) non-insulated terminals	1	\$63.00
<u>DN-CT-D4</u>	Die set for DN-CT-HDL; 24-8 AWG (0.25-10 mm ²) wire ferrules	1	\$63.00
<u>DN-CT-D5</u>	Die set for DN-CT-HDL; 6-4 AWG (16-25 mm ²) wire ferrules	1	\$63.00
<u>DN-CT-D6</u>	Die set for DN-CT-HDL; 2-1/0 AWG (35-50 mm ²) wire ferrules	1	\$63.00
<u>DN-CT-D7</u>	Die set for DN-CT-HDL; 22-10 AWG (0.5-6 mm ²) open barrel non-insulated terminals	1	\$99.00
<u>DN-CT-D8</u>	Die set for DN-CT-HDL; 8-pin (RJ45) modular plugs	1	\$63.00
<u>DN-CT-D9</u>	Die set for DN-CT-HDL; 6-pin (RJ11/RJ12) modular plugs	1	\$63.00
<u>DN-CT-SET</u>	Crimping tool modular system; includes handle and three die sets (DN-CT-HDL + DN-CT-D2 + DN-CT-D4 + DN-CT-D5) The die pairs are held together for easy handling, and interchange without separate tools.	1	\$188.00

* The DN-CT-xx series features a crimping tool with multiple interchangeable dies separately available. The die pairs are held together for easy handling, and can be interchanged without separate tools.



DN-CT-HDL
Crimping Tool



DN-CT-SET
Crimping Tool & Die Set

Wiring Accessories – Crimping Tool

DN-CT-Dx Interchangeable Crimping Dies (for DN-CT-xxx crimping tool only)

These dies are held together for easy handling, and can be interchanged without additional tools.

All DN-CT-Dx dies have been tested on leading brands of connectors to ensure quality connections.

Dies come in modular holders that can be connected together when not in use.



DN-CT-Dx die & holder



DN-CT-D1 (4300-3128)

Insulated Terminals & Connectors
26–22 AWG & 12–10 AWG

[Green & Yellow] (0.1–0.4 & 4–6 mm²)



DN-CT-D2 (4300-3129)

Insulated Terminals & Connectors
22–14 AWG

[Red & Blue] (0.5–2.5 mm²)



DN-CT-D3 (4300-3142)

Non-Insulated Terminals & Connectors
22–10 AWG (0.5–6 mm²)



DN-CT-D4 (4300-3127)

Wire Ferrules
24–8 AWG (0.25–10 mm²)



DN-CT-D5 (4300-3153)

Wire Ferrules
6–4 AWG (16–25 mm²)



DN-CT-D6 (4300-3154)

Wire Ferrules
2–1/0 AWG (35–50 mm²)



DN-CT-D7 (4300-3146)

Non-Insulated Open-Barrel Terminals
22–10 AWG (0.5–6 mm²)




DN-CT-D8 (4300-3144)

8-pin Modular Plugs
RJ45



DN-CT-D9 (4300-3132)

6-pin Modular Plugs
RJ11/RJ12



DN-CT-Dx Die Interchange Procedure