

# Roxburgh DRF Series EMI Filters

## Single-phase General Purpose EMI Filters - DIN Rail Mount

The Roxburgh DRF (DIN Rail Filter) Series single-stage filters are specifically designed as line filters for 120/240 VAC devices. Provides good performance for both common mode and

differential mode interference and are rated up to 250V. The DRF filters snap on to 35mm DIN rail for ease of mounting in cabinet hardware.

### Features

- 0-250 VAC/DC, 0-60 Hz, single-phase
- 1A - 10A models
- Molded plastic case
- Screw terminals
- 35mm DIN rail mount

Filter performance curves are available on item page at [www.AutomationDirect.com](http://www.AutomationDirect.com)

### Applications

- Ideally suited for products that must conform to part 15, FCC regulations
- Digital electronics
- Control power
- Measuring instruments
- Industrial and commercial controls and instrumentation

### Standards and Certifications



| DRF Series Filters    |         |                                        |
|-----------------------|---------|----------------------------------------|
| Part Number           | Price   | Description                            |
| <a href="#">DRF01</a> | \$56.00 | EMI Input Filter 120/240VAC, 1-ph, 1A  |
| <a href="#">DRF03</a> | \$56.00 | EMI Input Filter 120/240VAC, 1-ph, 3A  |
| <a href="#">DRF06</a> | \$56.00 | EMI Input Filter 120/240VAC, 1-ph, 6A  |
| <a href="#">DRF08</a> | \$53.00 | EMI Input Filter 120/240VAC, 1-ph, 8A  |
| <a href="#">DRF10</a> | \$56.00 | EMI Input Filter 120/240VAC, 1-ph, 10A |

| General Specifications             |                             |
|------------------------------------|-----------------------------|
| <b>Voltage Rating</b>              | 0-240V AC/DC, 0-60 Hz       |
| <b>Voltage Max.</b>                | 250V                        |
| <b>Voltage Withstand</b>           | 2100V AC/1 min              |
| <b>Phase</b>                       | 1                           |
| <b>UL/IEC Pollution Class</b>      | Degree II                   |
| <b>Humidity</b>                    | 93% RH (non-condensing)     |
| <b>Overload Current</b>            | 135% 2 hrs, 150% 60s        |
| <b>Insulation Resistance</b>       | 500VDC >3.5 M Ohms          |
| <b>Climate Class (IEC 60068-1)</b> | -25/85/21                   |
| <b>Temperature Rise</b>            | 45°C                        |
| <b>Temperature Rating</b>          | -13 to 185°F, -25°C to 85°C |
| <b>Flammability (UL94)</b>         | V-2                         |
| <b>Material</b>                    | Plastic Polyamide           |
| <b>Altitude*</b>                   | 1000m (3000m with derating) |
| <b>Mounting Clearance</b>          | >50mm Gap                   |
| <b>Agency Approval**</b>           | CE (EN60939-1)              |

\* Derate 1% per 100m after 1000m; Max 3000m.

\*\*To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific component part number web page.



# Roxburgh DRF Series EMI Filters

| Specifications                          |              |              |              |              |             |
|-----------------------------------------|--------------|--------------|--------------|--------------|-------------|
| Parameter                               | DRF01        | DRF03        | DRF06        | DRF08        | DRF10       |
| Max. Power (kW)                         | 0.2          | 0.7          | 1.4          | 1.9          | 2.4         |
| Current Rating (A)                      | 1            | 3            | 6            | 8            | 10          |
| SCCR Rating (kA)                        | 5            |              |              |              |             |
| Ingress Protection                      | IP20         |              |              |              |             |
| Terminal Style                          | Screw        |              |              |              |             |
| Torque (lb·in [N·m])                    | 4.4 [0.5]    |              |              |              |             |
| Max. Wire Gauge (mm <sup>2</sup> [AWG]) | 2.5 [14]     |              |              |              |             |
| Operational Leakage Current (mA)        | 0.75         |              |              |              |             |
| Total Resistance, Line to Load (mΩ)     | 640          | 71           | 19           | 15           | 12          |
| Residual Voltage (V@5s)                 | 1V@5s        |              |              |              |             |
| Heat Dissipation (W)                    | 0.64         |              | 0.66         | 0.96         | 1.2         |
| Weight, lb [kg]                         | 0.23 [0.105] | 0.21 [0.098] | 0.21 [0.099] | 0.23 [0.105] | 0.22 [0.10] |

| Temperature Derating Chart above 40°C* |             |            |      |      |      |      |      |      |      |      |
|----------------------------------------|-------------|------------|------|------|------|------|------|------|------|------|
| Continuous Ampacity at Ambient °C      | Part Number | Ambient °C |      |      |      |      |      |      |      |      |
|                                        |             | 40         | 45   | 50   | 55   | 60   | 65   | 70   | 75   | 80   |
|                                        | DRF01       | 1.00       | 0.93 | 0.87 | 0.79 | 0.72 | 0.64 | 0.55 | 0.44 | 0.31 |
|                                        | DRF03       | 3.00       | 2.80 | 2.60 | 2.38 | 2.15 | 1.91 | 1.64 | 1.33 | 0.93 |
|                                        | DRF06       | 6.00       | 5.60 | 5.19 | 4.76 | 4.31 | 3.82 | 3.28 | 2.65 | 1.86 |
|                                        | DRF08       | 8.00       | 7.47 | 6.92 | 6.35 | 5.74 | 5.09 | 4.37 | 3.54 | 2.48 |
|                                        | DRF10       | 10.00      | 9.34 | 8.65 | 7.94 | 7.18 | 6.36 | 5.46 | 4.42 | 3.10 |

\* NOTE: Using these filters above 40°C would comprise a non-UL application of device.

## Dimensions

mm [inches]

