



Drive Couplings

Accessories – Bore Reducers



Features

- For use in all SureMotion drive coupling hubs to reduce bore size
- Split-collar design with 2 set screw flats will not mark shaft
- 25% greater holding power than standard split collar
- Hardened stainless steel

Bore Reducers – Stainless Steel Clamping Type						
Part Number	Price	Outside Diameter		Inside Diameter		Length
		Nominal	Actual	Nominal	Actual	
DC-BRS04-02	\$16.50	1/4 in	0.250 in	1/8 in	0.125 in	0.221 in
DC-BRS04-04M	\$16.50			4mm	4mm	
DC-BRS04-03	\$16.50			3/16 in	0.1875 in	
DC-BRS04-05M	\$16.50			5mm	5mm	
DC-BRS08-06M	\$21.75	1/2 in	0.500 in	6mm	6mm	0.449 in
DC-BRS08-04	\$21.75			1/4 in	0.25 in	
DC-BRS08-05	\$22.00			5/16 in	0.3125 in	
DC-BRS08-08M	\$21.75			8mm	8mm	
DC-BRS08-06	\$22.00			3/8 in	0.375 in	
DC-BRS08-10M	\$22.00	5/8 in	0.625 in	10mm	10mm	0.460 in
DC-BRS10-10M	\$25.00			10mm	10mm	
DC-BRS10-07	\$25.00			7/16 in	0.4375 in	
DC-BRS10-12M	\$25.00			12mm	12mm	
DC-BRS10-08	\$25.00			1/2 in	0.5 in	
DC-BRS10-14M	\$25.00			14mm	14mm	
DC-BRS10-09	\$25.00	3/4 in	0.750 in	9/16 in	0.5625 in	0.646 in
DC-BRS12-06	\$30.00			3/8 in	0.375 in	
DC-BRS12-12M	\$30.00			12mm	12mm	
DC-BRS12-08	\$30.00			1/2 in	0.5 in	
DC-BRS12-10	\$30.00			5/8 in	0.625 in	
DC-BRS12-16M	\$30.00			16mm	16mm	
DC-BRS12-11	\$30.00	7/8 in	0.875 in	11/16 in	0.6875 in	0.755 in
DC-BRS14-14M	\$32.00			14mm	14mm	
DC-BRS14-10	\$32.00			5/8 in	0.625 in	
DC-BRS14-16M	\$32.00			16mm	16mm	
DC-BRS14-11	\$32.00			11/16 in	0.6875 in	
DC-BRS14-18M	\$32.00			18mm	18mm	
DC-BRS14-12	\$32.00	1 in	1.000 in	3/4 in	0.75 in	0.773 in
DC-BRS16-10	\$32.00			5/8 in	0.625 in	
DC-BRS16-18M	\$33.00			18mm	18mm	
DC-BRS16-12	\$33.00			3/4 in	0.75 in	
DC-BRS16-20M	\$33.00			20mm	20mm	
DC-BRS16-13	\$33.00			13/16 in	0.8125 in	
DC-BRS16-14	\$33.00	1-1/4 in	1.250 in	7/8 in	0.875 in	0.793 in
DC-BRS20-22M	\$34.00			22mm	22mm	
DC-BRS20-24M	\$34.00			24mm	24mm	
DC-BRS20-25M	\$34.00			25mm	25mm	
DC-BRS20-16	\$34.00			1 in	1.0 in	
DC-BRS20-17	\$34.00			1-1/16 in	1.0625 in	
DC-BRS20-18	\$34.00			1-1/8 in	1.125 in	