

# Cross Reference Guide



## CROSS REFERENCE GUIDE By manufacturers type reference or series number. Ampere ratings must be added for ordering purposes.

| FUSE TYPE                                   |                         | VOLT    | EDISON                    | BRUSH/<br>DORMAN | BUSSMANN  | MERSEN /<br>GOULD | GEC/CEFCO | LITTELFUSE |
|---------------------------------------------|-------------------------|---------|---------------------------|------------------|-----------|-------------------|-----------|------------|
| UL CLASS CURRENT LIMITING FUSES (CSA CLASS) |                         |         |                           |                  |           |                   |           |            |
| CC (HRCI-CC)                                | Time-Delay              | 600     | EDCC                      | –                | LP-CC     | ATDR              | –         | CCMR       |
|                                             | Time-Delay              | 600     | HCTR                      | –                | FNQ-R     | ATQR              | –         | KLDR       |
|                                             | Fast-Acting             | 600     | HCLR                      | HCLR             | KTK-R     | ATMR              | CTK-R     | KLKR       |
| RK1                                         | Time-Delay Dual Element | 250     | LENRK                     | –                | LPN-RK-SP | A2DR              | –         | LLNRK      |
|                                             |                         | 600     | LESRK                     | –                | LPS-RK-SP | A6DR              | –         | LLSRK      |
| RK5                                         | Time-Delay Dual Element | 250     | ECNR                      | –                | FRN-R     | TR                | –         | FLNR       |
|                                             |                         | 600     | ECSR                      | –                | FRS-R     | TRS               | –         | FLSR       |
| J                                           | Time-Delay Dual Element | 600     | JDL                       | –                | LPJ       | AJT               | –         | JTD        |
|                                             | High-Speed AC Drive     | 600     | JHL                       | –                | DFJ       | HSJ               | –         | –          |
| T                                           | Extremely Fast-Acting   | 300     | TJN                       | –                | JJN       | A3T               | –         | JLLN       |
|                                             |                         | 600     | TJS                       | –                | JJS       | A6T               | –         | JLLS       |
| UL CLASS GENERAL PURPOSE FUSES              |                         |         |                           |                  |           |                   |           |            |
| Midget                                      | Fast-Acting             | 600     | MCL                       | MCL              | KTK       | ATM               | CTK       | KLK        |
|                                             |                         | 250     | MOL                       | MOL              | BAF/BAN   | OTM               | –         | BLF        |
|                                             | Time-Delay              | 500     | MEQ                       | MEQ              | FNQ       | ATQ               | –         | FLQ        |
|                                             |                         | 250     | MEN                       | MEN              | FNM       | TRM               | –         | FLM        |
| 1/4"x 1-1/4" Ceramic                        | Fast-Acting             | 250/125 | ABC                       | ABC              | ABC       | GAB               | –         | 314        |
| 1/4"x 1-1/4" Glass                          |                         | 250/32  | AGC                       | AGC              | AGC       | GGC               | –         | 312        |
| 1/4"x 1-1/4" Ceramic                        | Time-Delay              | 250     | MDA                       | MDA              | MDA       | –                 | –         | 326        |
| 1/4"x 1-1/4" Glass                          |                         | 250/32  | MDL                       | MDL              | MDL       | GDL               | –         | 313        |
| 5x20 mm Glass                               | Fast-Acting             | 250/125 | GMA                       | GMA              | GMA       | GGM               | –         | 235        |
|                                             | Medium Time-Delay       | 250/125 | GMC                       | GMC              | GMC       | GSC               | –         | –          |
| 5x20 mm Glass                               | Fast-Acting             | 250     | S500                      | BDB              | GDB       | GSB               | –         | 217        |
|                                             | Time-Delay              | 250     | S506                      | BDC              | GDC       | GDG               | –         | 218        |
| Fuse Puller                                 |                         |         |                           |                  |           |                   |           |            |
| Fuse Puller FP-2                            |                         |         | old - 38072<br>new - FP-2 | –                | FP-2      | –                 | –         | –          |