

Enclosure Subpanels



Subpanels

Subpanels are not included with most enclosures and must be purchased separately.

The specifications table for each enclosure family list the part number of the subpanel that goes with each enclosure.

Subpanels for Small NEMA 12 (B) and NEMA 4 (BN4) Enclosures

- 14-gauge (painted, stainless, and galvanized)
- Painted steel subpanels are white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels fit the following enclosures: B, B_CH, BN4, BN4_CH, BN4_CHQT, BN4_SS, BN4_CHSS, BN4_CHSSA, BN4_CHQTSS, BN4_CHQTSSA ("_" refers to dimensions).



Subpanels for B and BN4 Enclosures					
Painted Steel	Price	304 Stainless Steel	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
<u>P0604</u>	\$5.25	<u>P0604SS</u>	\$15.25	6 x 4	4.88 x 2.88 [124 x 73]
<u>P0606</u>	\$6.25	<u>P0606SS</u>	\$19.00	6 x 6	4.88 x 4.88 [124 x 124]
<u>P0806</u>	\$7.25	<u>P0806SS</u>	\$22.50	8 x 6	6.88 x 4.88 [175 x 124]
<u>P0808</u>	\$8.50	—	—	8 x 8	6.88 x 6.88 [175 x 175]
<u>P1008</u>	\$9.25	<u>P1008SS</u>	\$32.50	10 x 8	8.88 x 6.88 [226 x 175]
<u>P1010</u>	\$11.50	—	—	10 x 10	8.88 x 8.88 [226 x 226]
<u>P1206</u>	\$9.25	—	—	12 x 6	10.88 x 4.88 [276 x 124]
<u>P1210</u>	\$13.25	<u>P1210SS</u>	\$45.50	12 x 10	10.88 x 8.88 [276 x 226]
<u>P1212</u>	\$15.50	<u>P1212SS</u>	\$53.00	12 x 12	10.88 x 10.88 [276 x 276]
<u>P1408</u>	\$12.75	—	—	14 x 8	12.88 x 6.88 [327 x 175]
<u>P1412</u>	\$17.50	<u>P1412SS</u>	\$61.00	14 x 12	12.88 x 10.88 [327 x 276]
<u>P1610</u>	\$17.00	—	—	16 x 10	14.88 x 8.88 [378 x 226]
<u>P1614</u>	\$23.00	<u>P1614SS</u>	\$80.00	16 x 14	14.88 x 12.88 [378 x 327]
Notes: Dimensions in inches [millimeters]. Letters in table correspond to letters on dimensional drawing.					

Dimensions

