


FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part features and extrusion core hole
- Material: varies by part



10 Series Bases

Fits  Slot Size 6



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link											
							Core Hole Attachment 1	T-Slot Attachment 2														
118356		\$16.00	n/a	1/4-20 UNC Transport/Base Plate	1 x 2in	n/a	161103 (2) included with kit		1	Die-cast zinc	PDF											
146399		\$16.00		3/8-16 UNC Transport/Base Plate							PDF											
151074		\$7.25		1/4-20 UNC x 1-1/2in Swivel Foot Threaded Rod with 15 mm ball	Transport/ Base Plate 118356	210 [463]*	n/a	n/a		Zinc plated steel	PDF											
151075		\$4.50		3/8-16 UNC x 1-1/2in Swivel Foot Threaded Rod with 15 mm ball	Transport/ Base Plate 146399	470 [1036]*				Zinc plated steel	PDF											
151068		\$4.00	1.57 in [39.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]				Nylon	PDF											
151071		\$9.50				3000 [6614]				Die-cast zinc	PDF											
151072		\$17.00	3.11 in [79.0 mm]								PDF											
151073		\$17.00									PDF											
151069		\$6.00	900 [1984]							Nylon	PDF											
151070		\$6.00									PDF											
151255		\$10.00	3.90 in [99.0 mm]			900 [1984]					PDF											
151256		\$10.00									PDF											

*Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]


Swivel foot assembly load rating = 210kg [463lb]

FATH® T-Slotted Rail Accessories

Bases - Continued

10 Series Bases - continued

Fits 



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
							Core Hole Attachment 1	**T-Slot Attachment 2			
151257		\$24.00	3.90 in [99.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	3500 [7716]	n/a	n/a	1	Die-cast zinc	PDF
151258		\$24.00									PDF
162933		\$12.50	See Drawing Link	Extended Swivel Base	Any 15mm ball Threaded Rod	1000 [2204]				Nylon	PDF
162934		\$27.00				3000 [6613]				Die-cast zinc	PDF
162955		\$10.00	n/a	Floor Bracket	1 x 1in, 1 x 2in, 2 x 2in	n/a		151040		Anodized aluminum	PDF

*Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]


Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]


**T-Slot nut also required

Bases Installation

Swivel Foot




Floor Bracket



FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part



15 Series Bases

Fits 



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link									
							Core Hole Attachment 1	*T-Slot Attachment 2												
118357		\$17.00	n/a	3/8-16 UNC Transport/Base Plate	1.5 x 3in	n/a	161105 (2) included with kit	n/a	1	Die-cast zinc	PDF									
161043		\$28.00			3 x 3in		161105 (4) included with kit				PDF									
151075		\$4.50		3/8-16 UNC x 1-1/2in Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 118357 and 161043	470 [1036]**	Zinc plated steel			PDF										
151068		\$4.00	1.57 in [39.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]	Nylon			PDF										
151071		\$9.50				3000 [6614]				Die-cast zinc	PDF									
151072		\$17.00	3.11 in [79.0 mm]								PDF									
151073		\$17.00									PDF									
151069		\$6.00	900 [1984]				Nylon			PDF										
151070		\$6.00								PDF										
151255		\$10.00								3.90 in [99.0 mm]								PDF		
151256		\$10.00																PDF		
151257		\$24.00	3500 [7716]				Die-cast zinc			PDF										
151258		\$24.00								PDF										

*T-Slot Nut also required

**Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]


Swivel foot assembly load rating = 210kg [463lb]

FATH® T-Slotted Rail Accessories

Bases - Continued

15 Series Bases - continued

Fits 



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link					
							Core Hole Attachment 1	*T-Slot Attachment 2								
162933		\$12.50	See 2D drawing	Extended Swivel Base	Any 15mm ball Threaded Rod	1000 [2204]	n/a	n/a	1	Nylon	PDF					
162934		\$27.00				3000 [6613]				Die-cast zinc	PDF					
166333		\$30.00	n/a	Foot Console	1.5 x 1.5 in, 3 x 3in	n/a		161054		Die-cast aluminum	PDF					
166334		\$30.00									PDF					
166335		\$30.00			1.5 x 3in, 3 x 3in						PDF					
166336		\$30.00									PDF					
162957		\$11.50		Floor Bracket	1.5 x 1.5 in, 1.5 x 3in, 3 x 3in			151100			Anodized aluminum	PDF				

*T-Slot Nut also required

**Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:


Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]

FATH® T-Slotted Rail Accessories


Bases - Continued



FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part



30 Series Bases

Fits Slot Size 8



Part Number	Part Image	Price	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link	
						Core Hole Attachment 1	***T-Slot Attachment 2				
162940		\$11.00	M8-1.25 Transport/ Base Plate	30 x 60mm	n/a	161102** (2) included with kit		1	Die-cast zinc	PDF	
162941		\$11.00	M10-1.5 Transport/ Base Plate							PDF	
162942		\$11.00	M12-1.75 Transport/ Base Plate							PDF	
162943		\$17.50	M8-1.25 Transport/ Base Plate	60 x 60mm		161102** (4) included with kit	n/a				PDF
162944		\$17.75	M10-1.5 Transport/ Base Plate								PDF
162945		\$20.00	M12-1.75 Transport/ Base Plate								PDF
162946		\$20.00	M14-2.0 Transport/ Base Plate								PDF
162947		\$20.00	M16-2.0 Transport/ Base Plate								PDF
151201		\$3.75	M8-1.25 x 40mm Swivel Foot Threaded Rod with 15mm ball	Requires Transport / Base Plate 162940 or 162943	350 [772]*	n/a		Zinc plated steel	PDF		
151202		\$4.00	M10-1.5 x 45mm Swivel Foot Threaded Rod with 15 mm ball	Requires Transport / Base Plate 162941 or 162944	470 [1036]*				PDF		
162938		\$6.50	M16-2.0 x 100mm Swivel Foot Threaded Rod with 15mm ball	Requires Transport / Base Plate 162947	1450 [3197]				PDF		

*Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]

**Requires tapping Core Hole (M8-1.25 x 20mm deep)

***T-Slot Nut also required.

FATH® T-Slotted Rail Accessories


Bases - Continued

30 Series Bases - continued												
		Fits		Slot Size 8		30 Series (mm) 30x30 30x60 60x60						
Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link	
							Core Hole Attachment 1	***T-Slot Attachment 2				
151068		\$4.00	1.57 in [39.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]	n/a	n/a	1	Nylon	PDF	
151071		\$9.50								PDF		
151072		\$17.00	3000 [6614]			Die-cast zinc				PDF		
151073		\$17.00								PDF		
151069		\$6.00								900 [1984]	Nylon	PDF
151070		\$6.00										PDF
162933		\$12.50	see 2D drawing	Extended Swivel Base	1000 [2204]				Nylon	PDF		
162934		\$27.00			3000 [6613]				Die-cast zinc	PDF		
162956		\$11.00	n/a	Floor Bracket	30 x 30mm, 30 x 60mm, 60 x 60mm	n/a		161066		Anodized aluminum	PDF	

*Based on installation with Transport / Base Plate
Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.
Example:
Threaded rod load rating = 210kg [463lb]
Swivel base load rating = 3000kg [6614lb]
Swivel foot assembly load rating = 210kg [463lb]
**Requires tapping Core Hole (M8-1.25 x 20mm deep)
***T-Slot Nut also required.

FATH® T-Slotted Rail Accessories


Bases - Continued



FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part features and extrusion core hole
- Material: varies by part



40 Series Bases

Fits  Slot Size 8



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
							Core Hole Attachment ①	*T-Slot Attachment ②			
151232		\$16.50	n/a	M12-1.75 Transport/Base Plate	40 x 80mm	n/a	161105 (2) included with kit	n/a	1	Die-cast zinc	PDF
151233		\$23.00			80 x 80mm		161105 (4) included with kit				PDF
162948		\$20.00		M16-2.0 Transport/Base Plate	40 x 80mm		161105 (2) included with kit				PDF
162949		\$25.00			80 x 80mm		161105 (4) included with kit				PDF
162950		\$25.00		M20-2.5 Transport/Base Plate							PDF
151231		\$4.50	1.57 in [39.0 mm]	M12-1.75 x 66mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 151232 or 151233	770 [1698]**	n/a	n/a	1	Zinc plated steel	PDF
162938		\$6.50		M16-2.0 x 100mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 162948 or 162949	1450 [3197]					PDF
162939		\$11.00		M20-2.5 x 150mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 162950	2430 [5357]					PDF
151068		\$4.00		Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]				Nylon	PDF
151071		\$9.50				3000 [6614]				Die-cast zinc	PDF

*T-Slot Nut also required.

**Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:


Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]

FATH® T-Slotted Rail Accessories

Bases - Continued

40 Series Bases - Continued															
		Fits		Slot Size 											
Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link				
							Core Hole Attachment 1	*T-Slot Attachment 2							
151069		\$6.00	3.11 in [79.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]	n/a	n/a	1	Nylon	PDF				
151070		\$6.00				PDF									
151255		\$10.00	3.90 in [99.0 mm]			900 [1984]					PDF				
151256		\$10.00				PDF									
151257		\$24.00				3500 [7716]				Die-cast zinc	PDF				
151258		\$24.00									PDF				
162933		\$12.50	See 2D drawing	Extended Swivel Base	Any 15mm ball Threaded Rod	1000 [2204]	n/a	n/a	1	Nylon	PDF				
162934		\$27.00				3000 [6613]				Die-cast zinc	PDF				
*T-Slot Nut also required. Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod. Example: Threaded rod load rating = 210kg [463lb] Swivel base load rating = 3000kg [6614lb] Swivel foot assembly load rating = 210kg [463lb]															


FATH® T-Slotted Rail Accessories

Bases - Continued

40 Series Bases - Continued

Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
							Core Hole Attachment 1	*T-Slot Attachment 2			
162889		\$24.50	n/a	Foot Console	40 x 40mm, 40 x 80mm	n/a	n/a	161068	1	Die-cast aluminum	PDF
166391		\$33.00									PDF
162890		\$25.50									PDF
166392		\$35.00									PDF
162960		\$47.00		Support Bracket	40 x 80mm, 80 x 80mm			M8-1.25 x 30mm (not sold by ADC)			PDF
162958		\$11.50		Floor Bracket	All 40 Series			161068		Anodized aluminum	PDF


*T-Slot Nut also required.



FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part features and extrusion core hole
- Material: varies by part



45 Series Bases

Fits Slot Size
10



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
							Core Hole Attachment 1	*T-Slot Attachment 2			
151259		\$20.50	n/a	M12-1.75 Transport/ Base Plate	45 x 90mm	n/a	161111 (2) included with kit	n/a	1	Die-cast zinc	PDF
151260		\$25.00		M12-1.75 Transport/ Base Plate	90 x 90mm		161111 (4) included with kit				PDF
162951		\$20.00		M16-2.0 Transport/ Base Plate	45 x 90mm		161111 (2) included with kit				PDF
162952		\$20.00		M20-2.5 Transport/ Base Plate	45 x 90mm		161111 (2) included with kit				PDF
162953		\$25.00		M16-2.0 Transport/ Base Plate	90 x 90mm		161111 (4) included with kit				PDF
162954		\$25.00		M20-2.5 Transport/ Base Plate	90 x 90mm		161111 (4) included with kit				PDF
151231		\$4.50		M12-1.75 x 66mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 151259 or 151260	770 [1698]**	n/a			Zinc plated steel	PDF
162938		\$6.50		M16-2.0 x 100mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 162951 or 162953	1450 [3197]**					PDF
162939		\$11.00		M20-2.5 x 150mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 162952 or 162954	2430 [5357]**					PDF
151068		\$4.00	1.57 in [39.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]				Nylon	PDF
151071		\$9.50				3000 [6614]				Die-cast zinc	PDF

*T-Slot Nut also required.

**Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]

FATH® T-Slotted Rail Accessories

Bases - Continued

45 Series Bases - continued																
Fits Slot Size 10						45 Series (mm) 45x45 45x90 90x90										
Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link					
							Core Hole Attachment 1	*T-Slot Attachment 2								
151072		\$17.00	3.11 in [79.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	3000 [6614]	n/a	n/a	1	Die-cast zinc	PDF					
151073		\$17.00				PDF										
151069		\$6.00				900 [1984]				Nylon	PDF					
151070		\$6.00									PDF					
151255		\$10.00	3.90 in [99.0 mm]			900 [1984]										
151256		\$10.00									PDF					
151257		\$24.00	3.90 in [99.0 mm]			3500 [7716]				Die-cast zinc	PDF					
151258		\$24.00									PDF					
162933		\$12.50	See 2D drawing	Extended Swivel Base	Any 15mm ball Threaded Rod	1000 [2204]				Nylon	PDF					
162934		\$27.00				3000 [6613]				Die-cast zinc	PDF					
162959		\$12.50	n/a	Floor Bracket	All 45 Series	n/a		161068		Anodized aluminum	PDF					
*T-Slot Nut also required. **Based on installation with Transport / Base Plate Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod. Example: Threaded rod load rating = 210kg [463lb] Swivel base load rating = 3000kg [6614lb] Swivel foot assembly load rating = 210kg [463lb]																

FATH® T-Slotted Rail Accessories

Bases - Continued

