


FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part features and extrusion core hole
- Material: varies by part



10 Series Bases

Fits Slot Size
6



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link										
							Core Hole Attachment 1	T-Slot Attachment 2													
118356		\$16.00	n/a	1/4-20 UNC Transport/Base Plate	1 x 2in	n/a	161103 (2) included with kit		1	Die-cast zinc	PDF										
146399		\$16.00		3/8-16 UNC Transport/Base Plate							PDF										
151074		\$7.25		1/4-20 UNC x 1-1/2in Swivel Foot Threaded Rod with 15 mm ball	Transport/ Base Plate 118356	210 [463]*	n/a			Zinc plated steel	PDF										
151075		\$4.50		3/8-16 UNC x 1-1/2in Swivel Foot Threaded Rod with 15 mm ball	Transport/ Base Plate 146399	470 [1036]*				Zinc plated steel	PDF										
151068		\$4.00	1.57 in [39.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]				Nylon	PDF										
151071		\$9.50				3000 [6614]				Die-cast zinc	PDF										
151072		\$17.00	3.11 in [79.0 mm]								PDF										
151073		\$17.00									PDF										
151069		\$6.00	900 [1984]							Nylon	PDF										
151070		\$6.00									PDF										
151255		\$10.00	3.90 in [99.0 mm]			900 [1984]					PDF										
151256		\$10.00									PDF										

*Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]


Swivel foot assembly load rating = 210kg [463lb]

FATH® T-Slotted Rail Accessories

Bases - Continued

10 Series Bases - continued

Fits 



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
							Core Hole Attachment 1	**T-Slot Attachment 2			
151257		\$24.00	3.90 in [99.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	3500 [7716]	n/a	n/a	1	Die-cast zinc	PDF
151258		\$24.00									PDF
162933		\$12.50	See Drawing Link	Extended Swivel Base	Any 15mm ball Threaded Rod	1000 [2204]				Nylon	PDF
162934		\$27.00				3000 [6613]					PDF
162955		\$10.00	n/a	Floor Bracket	1 x 1in, 1 x 2in, 2 x 2in	n/a		151040		Anodized aluminum	PDF

*Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]


Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]


**T-Slot nut also required

Bases Installation

Swivel Foot




Floor Bracket



FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part



15 Series Bases

Fits
Slot Size
8



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link		
							Core Hole Attachment ①	*T-Slot Attachment ②					
118357		\$17.00	n/a	3/8-16 UNC Transport/Base Plate	1.5 x 3in	n/a	161105 (2) included with kit	n/a	1	Die-cast zinc	PDF		
161043		\$29.50			3 x 3in		161105 (4) included with kit				PDF		
151075		\$4.50		3/8-16 UNC x 1-1/2in Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 118357 and 161043	470 [1036]**	PDF						
151068		\$4.00	1.57 in [39.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]	n/a			1	Nylon	PDF	
151071		\$9.50										PDF	
151072		\$17.00	3.11 in [79.0 mm]								3000 [6614]	Die-cast zinc	PDF
151073		\$17.00									PDF		
151069		\$6.00									900 [1984]		Nylon
151070		\$6.00										PDF	
151255		\$10.00				3.90 in [99.0 mm]							
151256		\$10.00										PDF	
151257		\$24.00									3500 [7716]	Die-cast zinc	PDF
151258		\$24.00											PDF

*T-Slot Nut also required

**Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:


Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]


FATH® T-Slotted Rail Accessories

Bases - Continued

15 Series Bases - continued													
		Fits		Slot Size		15 Series (inch)							
				8									
Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link		
							Core Hole Attachment 1	*T-Slot Attachment 2					
162933		\$12.50	See 2D drawing	Extended Swivel Base	Any 15mm ball Threaded Rod	1000 [2204]	n/a		n/a		Nylon	PDF	
162934		\$27.00				3000 [6613]					Die-cast zinc	PDF	
166333		\$30.00	n/a	Foot Console	1.5 x 1.5 in, 3 x 3in				161054	1	Die-cast aluminum	PDF	
166334		\$30.00										PDF	
166335		\$30.00			1.5 x 3in, 3 x 3in							PDF	
166336		\$30.00										PDF	
162957		\$11.50		Floor Bracket	1.5 x 1.5 in, 1.5 x 3in, 3 x 3in					151100		Anodized aluminum	PDF
*T-Slot Nut also required **Based on installation with Transport / Base Plate Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod. Example: Threaded rod load rating = 210kg [463lb] Swivel base load rating = 3000kg [6614lb] Swivel foot assembly load rating = 210kg [463lb]													

FATH[®] T-Slotted Rail Accessories


Bases - Continued



FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part



30 Series Bases

Fits Slot Size 8



Part Number	Part Image	Price	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link			
						Core Hole Attachment 1	***T-Slot Attachment 2						
162940		\$11.50	M8-1.25 Transport/ Base Plate	30 x 60mm	n/a	161102** (2) included with kit	n/a	1	Die-cast zinc	PDF			
162941		\$11.50	M10-1.5 Transport/ Base Plate							PDF			
162942		\$11.50	M12-1.75 Transport/ Base Plate							PDF			
162943		\$17.50	M8-1.25 Transport/ Base Plate	60 x 60mm		161102** (4) included with kit				n/a	1	Die-cast zinc	PDF
162944		\$17.75	M10-1.5 Transport/ Base Plate										PDF
162945		\$20.00	M12-1.75 Transport/ Base Plate										PDF
162946		\$20.00	M14-2.0 Transport/ Base Plate										PDF
162947		\$20.00	M16-2.0 Transport/ Base Plate										PDF
151201		\$3.75	M8-1.25 x 40mm Swivel Foot Threaded Rod with 15mm ball	Requires Transport / Base Plate 162940 or 162943	350 [772]*	n/a		Zinc plated steel	PDF				
151202		\$4.00	M10-1.5 x 45mm Swivel Foot Threaded Rod with 15 mm ball	Requires Transport / Base Plate 162941 or 162944	470 [1036]*				PDF				
162938		\$6.50	M16-2.0 x 100mm Swivel Foot Threaded Rod with 15mm ball	Requires Transport / Base Plate 162947	1450 [3197]				PDF				

*Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]

**Requires tapping Core Hole (M8-1.25 x 20mm deep)

***T-Slot Nut also required.


FATH® T-Slotted Rail Accessories

Bases - Continued

30 Series Bases - continued												
		Fits		Slot Size 8		30 Series (mm) 30x30 30x60 60x60						
Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link	
							Core Hole Attachment 1	***T-Slot Attachment 2				
151068		\$4.00	1.57 in [39.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]	n/a	n/a	1	Nylon	PDF	
151071		\$9.50								PDF		
151072		\$17.00	3.11 in [79.0 mm]			3000 [6614]				Die-cast zinc	PDF	
151073		\$17.00									PDF	
151069		\$6.00									Nylon	PDF
151070		\$6.00										PDF
162933		\$12.50	see 2D drawing	Extended Swivel Base	1000 [2204]	Nylon	PDF					
162934		\$27.00			3000 [6613]	Die-cast zinc	PDF					
162956		\$11.00	n/a	Floor Bracket	30 x 30mm, 30 x 60mm, 60 x 60mm	n/a	161066	Anodized aluminum	PDF			
*Based on installation with Transport / Base Plate Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod. Example: Threaded rod load rating = 210kg [463lb] Swivel base load rating = 3000kg [6614lb] Swivel foot assembly load rating = 210kg [463lb] **Requires tapping Core Hole (M8-1.25 x 20mm deep) ***T-Slot Nut also required.												

FATH® T-Slotted Rail Accessories


Bases - Continued



FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part features and extrusion core hole
- Material: varies by part



40 Series Bases

Fits  Slot Size 8



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
							Core Hole Attachment ①	*T-Slot Attachment ②			
151232		\$16.50	n/a	M12-1.75 Transport/Base Plate	40 x 80mm	n/a	161105 (2) included with kit	n/a	1	Die-cast zinc	PDF
151233		\$23.00			80 x 80mm		161105 (4) included with kit				PDF
162948		\$20.00		M16-2.0 Transport/Base Plate	40 x 80mm		161105 (2) included with kit				PDF
162949		\$25.00			80 x 80mm		161105 (4) included with kit				PDF
162950		\$25.00		M20-2.5 Transport/Base Plate							PDF
151231		\$4.50	1.57 in [39.0 mm]	M12-1.75 x 66mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 151232 or 151233	770 [1698]**	n/a	n/a	1	Zinc plated steel	PDF
162938		\$6.50		M16-2.0 x 100mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 162948 or 162949	1450 [3197]					PDF
162939		\$11.00		M20-2.5 x 150mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 162950	2430 [5357]					PDF
151068		\$4.00		Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]				Nylon	PDF
151071		\$9.50				3000 [6614]				Die-cast zinc	PDF

*T-Slot Nut also required.

**Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:


Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]

FATH® T-Slotted Rail Accessories


Bases - Continued

40 Series Bases - Continued															
		Fits 													
Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link				
							Core Hole Attachment 1	*T-Slot Attachment 2							
151069		\$6.00	3.11 in [79.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]	n/a	n/a	1	Nylon	PDF				
151070		\$6.00				PDF									
151255		\$10.00	3.90 in [99.0 mm]			900 [1984]					PDF				
151256		\$10.00				PDF									
151257		\$24.00				3500 [7716]				Die-cast zinc	PDF				
151258		\$24.00									PDF				
162933		\$12.50	See 2D drawing	Extended Swivel Base	Any 15mm ball Threaded Rod	1000 [2204]	n/a	n/a	1	Nylon	PDF				
162934		\$27.00				3000 [6613]				Die-cast zinc	PDF				
*T-Slot Nut also required. Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod. Example: Threaded rod load rating = 210kg [463lb] Swivel base load rating = 3000kg [6614lb] Swivel foot assembly load rating = 210kg [463lb]															


FATH® T-Slotted Rail Accessories

Bases - Continued

40 Series Bases - Continued

Fits Slot Size 8 40 Series (mm) 											
Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
							Core Hole Attachment 1	*T-Slot Attachment 2			
162889		\$24.50	n/a	Foot Console	40 x 40mm, 40 x 80mm	n/a	n/a	161068	1	Die-cast aluminum	PDF
166391		\$33.00									PDF
162890		\$25.50									PDF
166392		\$35.00									PDF
162960		\$47.00		Support Bracket	40 x 80mm, 80 x 80mm			M8-1.25 x 30mm (not sold by ADC)			PDF
162958		\$11.50		Floor Bracket	All 40 Series			161068		Anodized aluminum	PDF


*T-Slot Nut also required.



FATH® T-Slotted Rail Accessories


Bases

- Recommended ADC Fastener based on part features and extrusion core hole
- Material: varies by part



45 Series Bases

Fits Slot Size
10



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
							Core Hole Attachment 1	*T-Slot Attachment 2			
151259		\$20.50	n/a	M12-1.75 Transport/ Base Plate	45 x 90mm	n/a	161111 (2) included with kit	n/a	1	Die-cast zinc	PDF
151260		\$25.00			90 x 90mm		161111 (4) included with kit				PDF
162951		\$20.00		M16-2.0 Transport/ Base Plate	45 x 90mm		161111 (2) included with kit				PDF
162952		\$20.00		M20-2.5 Transport/ Base Plate	45 x 90mm		161111 (2) included with kit				PDF
162953		\$25.00		M16-2.0 Transport/ Base Plate	90 x 90mm		161111 (4) included with kit				PDF
162954		\$25.00		M20-2.5 Transport/ Base Plate	90 x 90mm		161111 (4) included with kit				PDF
151231		\$4.50		M12-1.75 x 66mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 151259 or 151260	770 [1698]**	n/a			Zinc plated steel	PDF
162938		\$6.50		M16-2.0 x 100mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 162951 or 162953	1450 [3197]**					PDF
162939		\$11.00		M20-2.5 x 150mm Swivel Foot Threaded Rod with 15mm ball	Transport/Base Plate 162952 or 162954	2430 [5357]**					PDF
151068		\$4.00	1.57 in [39.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	900 [1984]				Nylon	PDF
151071		\$9.50				3000 [6614]				Die-cast zinc	PDF

*T-Slot Nut also required.

**Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]


Swivel foot assembly load rating = 210kg [463lb]

FATH® T-Slotted Rail Accessories

Bases - Continued

45 Series Bases - continued

Fits 



Part Number	Part Image	Price	Diameter	Description	Fits	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link
							Core Hole Attachment 1	*T-Slot Attachment 2			
151072		\$17.00	3.11 in [79.0 mm]	Swivel Base With Anti-Slip Plate	Any 15mm ball Threaded Rod	3000 [6614]	n/a	n/a	1	Die-cast zinc	PDF
151073		\$17.00									PDF
151069		\$6.00				900 [1984]				Nylon	PDF
151070		\$6.00									PDF
151255		\$10.00	3.90 in [99.0 mm]			900 [1984]				PDF	
151256		\$10.00								PDF	
151257		\$24.00	3.90 in [99.0 mm]			3500 [7716]				Die-cast zinc	PDF
151258		\$24.00									PDF
162933		\$12.50	See 2D drawing	Extended Swivel Base	Any 15mm ball Threaded Rod	1000 [2204]				Nylon	PDF
162934		\$27.00				3000 [6613]				Die-cast zinc	PDF
162959		\$12.50	n/a	Floor Bracket	All 45 Series	n/a		161068		Anodized aluminum	PDF

*T-Slot Nut also required.

**Based on installation with Transport / Base Plate

Load rating of a swivel foot assembly is based on the part with the lowest load rating, typically the threaded rod.

Example:

Threaded rod load rating = 210kg [463lb]

Swivel base load rating = 3000kg [6614lb]

Swivel foot assembly load rating = 210kg [463lb]

FATH® T-Slotted Rail Accessories

Bases - Continued

