

FATH® T-Slotted Rail Accessories


Casters

- Recommended ADC Fastener based on part feature and attachment type
- Material: varies by part


10 Series Casters									
Fits		Slot Size 6	10 Series (Inch) 1x1 1x2 2x2						
Part Number	Part Image	Price	Description	Load Rating kg [lb]	Requires	Recommended Screw Fastener *T-Slot Attachment 2 (ADC Part Number)	Pack Quantity	Material	Drawing Link
163010		\$40.00	Leveling Caster with M12-1.75 x 35mm threaded stud (included)	250 [551]	Transport / Base Plate with M12-1.75 threaded hole	n/a	1	Die-cast aluminum/ steel/nylon/ rubber	PDF
163011		\$52.00		500 [1102]					PDF
163012		\$41.00	Leveling Caster With Mounting Plate	250 [551]	n/a	BHCS 1/4-20x7/16" (not sold by ADC)			PDF
163013		\$56.00		500 [1102]					PDF
*T-Slot Nut with 1/4 washer also required.									

Caster Installation

Leveling Caster with M12-1.75 x 35mm threaded stud




Leveling Caster with mounting plate




FATH® T-Slotted Rail Accessories

Casters


- Recommended ADC Fastener based on part feature and attachment type
- Material: varies by part

15 Series Casters											
Fits		Slot Size 8		15 Series (inch)    1.5x1.5 1.5x3 3x3							
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link	
						Core Hole Attachment 1	*T-Slot Attachment 2				
151134		\$47.00	Swivel Caster (requires Swivel Caster Adapter Plate 151136)	n/a	122 [269]	161107	n/a	1	Thermoplastic polyurethane/ nylon/steel	PDF	
151135		\$40.50	Fixed Caster (requires Fixed Fixed Caster Adapter Plate 161040)			161106				PDF	
151136		\$4.50	3 Swivel Caster Adapter Plate	Requires Swivel Caster 151134)	n/a	n/a	Steel		PDF		
161040		\$3.50	3 Fixed Fixed Caster Adapter Plate	Requires Fixed Caster 151135)			Die-cast zinc		PDF		
151137		\$62.00	Swivel Caster	n/a	122 [269]	n/a	161053		Thermoplastic polyurethane/ nylon/steel	PDF	
151138		\$49.00	Fixed Caster				PDF				
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]		n/a	Die-cast aluminum/ steel/nylon/ rubber	PDF		
163011		\$52.00			500 [1102]				PDF		
163012		\$41.00		n/a	250 [551]		151040			PDF	
163013		\$56.00			500 [1102]					PDF	
*T-Slot Nut also required											

*T-Slot Nut also required

FATH[®] T-Slotted Rail Accessories


Casters - Continued



FATH® T-Slotted Rail Accessories

Casters


- Recommended ADC Fastener based on part feature and attachment type
- Material: varies by part

30 Series Casters												
		Fits 										
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link		
						Core Hole Attachment 1	*T-Slot Attachment 2					
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]	n/a	n/a	1	Die-cast aluminum/ steel/nylon/ rubber	PDF		
163011		\$52.00			500 [1102]					PDF		
163012		\$41.00		n/a	250 [551]		161059			PDF		
163013		\$56.00			500 [1102]					PDF		
*T-Slot Nut also required.												


*T-Slot Nut also required.

Caster Installation

Leveling Caster with bolt hole thread



Leveling Caster with mounting plate



FATH® T-Slotted Rail Accessories

Casters


- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part

40 Series Casters												
		Slot Size 8		40 Series (mm) 40x40 40x80 80x80								
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link		
						Core Hole Attachment 1	*T-Slot Attachment 2					
151134		\$47.00	Swivel Caster (requires Swivel Caster Adapter Plate 151136)	n/a	122 [269]	161107	n/a	1	Thermoplastic polyurethane/ nylon/steel	PDF		
151135		\$40.50	Fixed Caster (requires Fixed Fixed Caster Adapter Plate 161040)			161106				PDF		
151136		\$4.50	3 Swivel Caster Adapter Plate	Requires Swivel Caster 151134	n/a				Steel	PDF		
161040		\$3.50	3 Fixed Fixed Caster Adapter Plate	Requires Fixed Caster 151135					Die-cast zinc	PDF		
151137		\$62.00	Swivel Caster	n/a	122 [269]	n/a	161053		Thermoplastic polyurethane/ nylon/steel	PDF		
151138		\$49.00	Fixed Caster							PDF		
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]		n/a		Die-cast aluminum/ steel/nylon/ rubber	PDF		
163011		\$52.00			500 [1102]					PDF		
163012		\$41.00		n/a	250 [551]		161060			PDF		
163013		\$56.00			500 [1102]					PDF		
*T-Slot Nut also required												

*T-Slot Nut also required

FATH[®] T-Slotted Rail Accessories

Casters - Continued



FATH® T-Slotted Rail Accessories

Casters

- Recommended ADC Fastener based on part feature and core hole
- Material: varies by part

45 Series Casters												
Fits		Slot Size		45 Series (mm)								
				  								
Part Number	Part Image	Price	Description	Requires	Load Rating kg [lb]	Recommended Screw Fastener (ADC Part Number)		Pack Quantity	Material	Drawing Link		
						Core Hole Attachment 1	*T-Slot Attachment 2					
151134		\$47.00	Swivel Caster	Requires Swivel Caster Adapter Plate 151261	122 [269]	161111	n/a	1	Thermoplastic polyurethane/ nylon/steel	PDF		
151135		\$40.50	Fixed Caster	Requires Fixed Caster Adapter Plate 161041		161110				PDF		
151261		\$4.50	3 Swivel Caster Adapter Plate	Requires Swivel Caster 151134	n/a	n/a			Steel	PDF		
161041		\$3.50	3 Fixed Caster Adapter Plate	Requires Fixed Caster 151135					Die-cast zinc	PDF		
151137		\$62.00	Swivel Caster	n/a	122 [269]	n/a	161066		Thermoplastic polyurethane/ nylon/steel	PDF		
151138		\$49.00	Fixed Caster				PDF					
163010		\$40.00	Leveling Caster	Transport / Base Plate with M12-1.75 threaded hole	250 [551]		n/a		Die-cast aluminum/ steel/nylon/ rubber	PDF		
163011		\$52.00			500 [1102]					PDF		
163012		\$41.00		n/a	250 [551]		161061			PDF		
163013		\$56.00			500 [1102]					PDF		
*T-Slot Nut also required												

*T-Slot Nut also required

FATH® T-Slotted Rail Accessories

Casters - Continued

