



















GCV Valve Replacement Coils

GCV Valve Replacement Coils									
Coil Photo	Part No.	Voltage Rating	Power Rating	Insulation	Connection	Cable Length	Fits Valve Series	Price	Weight (lbs)
	<u>HS3GN16A24</u>	24VDC	9W	Class H: 180°C (356°F)	1/2 in conduit w/ 18AWG pigtail	24.0 in	S211 series valves	\$67.00	0.55
	<u>HS3YN16</u>	24VDC	9W	Class H: 180°C (356°F)	18mm DIN style wiring plug	N/A	S211 series valves	\$67.00	0.5



GCV Valves Replacement Coils

Water Valve Accessory Coils									
Coil Photo	Part No.	Voltage Rating	Power Rating	Insulation	Connection	Cable Length	Fits Valve Series	Price	Weight (lbs)
	<u>HS4YN02</u>	120VAC	10W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4YN04</u>	240VAC	10W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4YN24</u>	24VAC	10W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4YN16</u>	24VDC	10W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves	\$49.00	0.6
	<u>HS4GN02A24</u>	120VAC	10W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4GN04A24</u>	240VAC	10W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4GN24A24</u>	24VAC	10W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S201, NS201, S301 and NS301 valves	\$49.00	0.6
	<u>HS4GN16A24</u>	24VDC	10W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S201, NS201, S211 DC, NS211 DC, S301 and NS301 valves	\$49.00	0.6
	<u>HS3YN02</u>	120VAC	8W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3YN04</u>	240VAC	8W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3YN24</u>	24VAC	8W	Class H: 180°C (356°F)	18mm (DIN 43650A) style wiring plug	N/A	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3GN02A24</u>	120VAC	88W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3GN04A24</u>	240VAC	8W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S211 and NS211 AC valves	\$41.00	0.5
	<u>HS3GN24A24</u>	24VAC	8W	Class H: 180°C (356°F)	1/2 in conduit 24in 18AWG pigtail	24.0 in	S211 and NS211 AC valves	\$41.00	0.5