

IP66 ABS Plastic Flanged Miniature Cases with Styled Lid



Features

- Ideally suited for mounting printed circuit boards.
- Can be used in a tabletop configuration or two different wall-mount configurations.
- Rounded corners and face provide a more modern look while still offering superior watertight ratings.
 - ABS plastic or ABS Versions are molded from general purpose material which carries a flammability rating of UL94-HB. For indoor use.
- Gasketed lid with two piece tongue and groove construction provides protection against oil, dust, and water.
- Lid is secured with included M4 stainless steel machine screws which are threaded into integral stainless steel bushings for repetitive assembly and disassembly. All hardware is stainless steel to avoid corrosion.
- Foot Kits available: ([1557FOOT2BK-24](#), [1557FOOT2GY-24](#), [1557FOOTGY-24](#), [1557FOOTBK-24](#))

Materials

- Available in black or gray.
- General Purpose ABS plastic
- Gasket is one piece made from high temperature, UL listed silicone.
 - Sold in pairs

Listings

- Complies with IEC 60529, IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

IP66 ABS Plastic Flanged Miniature Cases with Styled Lid

Black	Light Gray	Price	Enclosure Size HxWxD	Lid Depth	Drawing Link	Replacement Gasket	Price
1557BABK	1557BAGY	\$13.00	3.15 x 3.15 x 2.36 [80 x 80 x 60]	45 [1.77]	PDF	1557BGASKET	\$5.75
1557BBK	1557BGY	\$12.50	3.15 x 3.15 x 1.77 [80 x 80 x 45]	30 [1.18]	PDF	1557BGASKET	\$5.75
1557DABK	1557DAGY	\$19.25	4.72 x 4.72 x 2.76 [120 x 120 x 70]	56 [2.20]	PDF	1557DGASKET	\$5.75
1557DBK	1557DGY	\$14.75	4.72 x 4.72 x 1.77 [120 x 120 x 45]	31 [1.22]	PDF	1557DGASKET	\$5.75
1557FABK	1557FAGY	\$27.50	6.30 x 6.30 x 2.76 [160 x 160 x 70]	56 [2.20]	PDF	1557FGASKET	\$11.25
1557FBK	1557FGY	\$20.25	6.30 x 6.30 x 1.77 [160 x 160 x 45]	31 [1.22]	PDF	1557FGASKET	\$11.25
1557HABK	1557HAGY	\$28.50	7.87 x 7.87 x 2.76 [200 x 200 x 70]	56 [2.20]	PDF	1557HGASKET	\$11.25
1557HBK	1557HGY	\$27.50	7.87 x 7.87 x 1.77 [200 x 200 x 45]	31 [1.22]	PDF	1557HGASKET	\$11.25

Notes: Dimensions in inches [millimeters].