

Enclosure Accessories

Deep-Hinged Door with Window



Application

- Extra deep kits are designed to provide protection and easy access to components and equipment installed inside an enclosure.
- Maintain environmental protection level of NEMA 4 and 12 (NEMA 4X for stainless steel).
- Frame is 14-gauge mild steel or 316L stainless steel.
- 1/4-turn latch for easy access.
- 2.5 in [64 mm] of extra usable depth.
- Oil-resistant neoprene gasket ensures a watertight seal.
- Can be either left- or right-hand hinged.
- Window is 0.25 in [6.35mm] thick, UV-Resistant Polycarbonate.
- Conveniently sized to allow mounting on the door of any Hammond wall-mount enclosure or in any other Hammond enclosure with a suitable mounting surface.
- Mounting hardware and template are included.
- Finished in ANSI 61 gray recoatable powder or #4 brushed stainless steel.

Deep-Hinged Door with Window								
Carbon Steel	Price	Stainless Steel	Price	Drawing Link	Overall Dimensions HxWxD	Viewing Area YxZ	# of Latches	Maximum Cut-Out Size
1481WDH1418	\$548.00	1481WSSDH1418	\$1,303.00	PDF	12.19 x 14.56 x 2.75 [310 x 370 x 70]	8.00 x 9.17 [203 x 233]	1	
1481WDH1612	\$577.00	1481WSSDH1612	\$1,372.00	PDF	14.19 x 8.14 x 2.75 [360 x 207 x 70]	10.00 x 2.75 [254 x 70]	1	
1481WDH1620	\$690.00	—	—	PDF	14.19 x 16.14 x 2.75 [360 x 410 x 70]	10.00 x 10.75 [254 x 273]	1	
1481WDH1624	\$742.00	—	—	PDF	14.19 x 20.14 x 2.75 [360 x 512 x 70]	10.00 x 14.75 [254 x 375]	1	
1481WDH2016	\$690.00	1481WSSDH2016	\$1,640.00	PDF	18.19 x 12.14 x 2.75 [462 x 308 x 70]	14.00 x 6.75 [356 x 171]	1	
1481WDH2024	\$794.00	—	—	PDF	18.19 x 20.14 x 2.75 [462 x 512 x 70]	14.00 x 14.75 [356 x 375]	1	
1481WDH2416	\$742.00	1481WSSDH2416	\$1,760.00	PDF	22.19 x 12.14 x 2.75 [564 x 308 x 70]	18.00 x 6.75 [457 x 171]	1	
1481WDH2420	\$794.00	1481WSSDH2420	\$1,883.00	PDF	22.19 x 16.14 x 2.75 [564 x 410 x 70]	18.00 x 10.75 [457 x 273]	1	
1481WDH2430	\$949.00	1481WSSDH2430	\$2,247.00	PDF	22.19 x 26.14 x 2.75 [564 x 664 x 70]	18.00 x 20.75 [457 x 527]	1	
1481WDH3024	\$949.00	1481WSSDH3024	\$2,247.00	PDF	28.19 x 20.14 x 2.75 [716 x 512 x 70]	24.00 x 14.75 [610 x 375]	2	
1481WDH3624	\$1,104.00	1481WSSDH3624	\$2,612.00	PDF	34.19 x 20.14 x 2.75 [868 x 512 x 70]	30.00 x 14.75 [762 x 375]	2	

Note: Dimensions in inches [millimeters].

