

Enclosure Accessories

Floor Stand Kit



Application



- Kit includes two mounting feet and hardware kit.
- Pre-punched mounting feet may be used as a template to drill holes on bottom of enclosure.
- Finished in ANSI 61 gray powder coat or #4 brushed stainless steel.

304 Stainless Steel Floor Stand Kits

Part Number	Price	For Use with Enclosure Depth	Dimensions HxWxD	Drawing Link
1481FC8KSS	\$510.00	8.00 [203]	12.00 x 6.00 x 8.00 [305 x 152 x 203]	PDF
1481FC10KSS	\$498.00	10.00 [254]	12.00 x 8.00 x 10.00 [305 x 203 x 254]	PDF
1481FC12KSS	\$615.00	12.00 [305]	12.00 x 8.00 x 12.00 [305 x 203 x 305]	PDF
1481FC18KSS	\$745.00	18.00 [457]	12.00 x 8.00 x 18.00 [305 x 203 x 457]	PDF
1481FC20KSS	\$835.00	20.00 [508]	12.00 x 10.00 x 20.00 [305 x 254 x 508]	PDF
1481FC24KSS	\$838.00	24.00 [610]	12.00 x 10.00 x 24.00 [305 x 254 x 610]	PDF
1481FC16KSS	\$652.00	16.00 [406]	12.00 x 10.00 x 16.00 [305 x 254 x 406]	PDF
1481FK10KSS	\$869.00	10.00 [254]	24.00 x 8.00 x 10.00 [610 x 203 x 254]	PDF
1481FK12KSS	\$947.00	12.00 [305]	24.00 x 10.00 x 12.00 [610 x 254 x 305]	PDF

Note: Dimensions in inches [millimeters].

Painted Steel Floor Stand Kits

Part Number	Price	For Use with Enclosure Depth	Dimensions HxWxD	Drawing Link
1481FA8K	\$175.00	8.00 [203]	6.00 x 6.00 x 8.00 [152 x 152 x 203]	PDF
1481FA10K	\$192.00	10.00 [254]	6.00 x 8.00 x 10.00 [152 x 203 x 254]	PDF
1481FA12K	\$220.00	12.00 [305]	6.00 x 8.00 x 12.00 [152 x 203 x 305]	PDF
1481FA16K	\$234.00	16.00 [406]	6.00 x 10.00 x 16.00 [152 x 254 x 406]	PDF
1481FA18K	\$259.00	18.00 [457]	6.00 x 8.00 x 18.00 [152 x 203 x 457]	PDF
1481FA20K	\$316.00	20.00 [508]	6.00 x 10.00 x 20.00 [152 x 254 x 508]	PDF
1481FC6K	\$210.00	6.00 [152]	12.00 x 5.00 x 6.00 [305 x 127 x 152]	PDF
1481FC8K	\$226.00	8.00 [203]	12.00 x 6.00 x 8.00 [305 x 152 x 203]	PDF
1481FC10K	\$243.00	10.00 [254]	12.00 x 8.00 x 10.00 [305 x 203 x 254]	PDF
1481FC12K	\$259.00	12.00 [305]	12.00 x 8.00 x 12.00 [305 x 203 x 305]	PDF
1481FC16K	\$293.00	16.00 [406]	12.00 x 10.00 x 16.00 [305 x 254 x 406]	PDF
1481FC18K	\$311.00	18.00 [457]	12.00 x 8.00 x 18.00 [305 x 203 x 457]	PDF
1481FC20K	\$326.00	20.00 [508]	12.00 x 10.00 x 20.00 [305 x 254 x 508]	PDF
1481FC24K	\$364.00	24.00 [610]	12.00 x 10.00 x 24.00 [305 x 254 x 610]	PDF
1481FE6K	\$222.00	6.00 [152]	15.00 x 5.00 x 6.00 [381 x 127 x 152]	PDF
1481FE8K	\$252.00	8.00 [203]	15.00 x 6.00 x 8.00 [381 x 152 x 203]	PDF
1481FE10K	\$269.00	10.00 [254]	15.00 x 8.00 x 10.00 [381 x 203 x 254]	PDF
1481FE12K	\$286.00	12.00 [305]	15.00 x 8.00 x 12.00 [381 x 203 x 305]	PDF
1481FE16K	\$320.00	16.00 [406]	15.00 x 10.00 x 16.00 [381 x 254 x 406]	PDF
1481FE18K	\$339.00	18.00 [457]	15.00 x 10.00 x 18.00 [381 x 254 x 457]	PDF
1481FE24K	\$380.00	24.00 [610]	15.00 x 10.00 x 24.00 [381 x 254 x 610]	PDF
1481FG6K	\$235.00	6.00 [152]	18.00 x 5.00 x 6.00 [457 x 127 x 152]	PDF
1481FG8K	\$276.00	8.00 [203]	18.00 x 8.00 x 8.00 [457 x 203 x 203]	PDF
1481FG10K	\$293.00	10.00 [254]	18.00 x 8.00 x 10.00 [457 x 203 x 254]	PDF
1481FG12K	\$311.00	12.00 [305]	18.00 x 8.00 x 12.00 [457 x 203 x 305]	PDF
1481FK10K	\$344.00	10.00 [254]	24.00 x 8.00 x 10.00 [610 x 203 x 254]	PDF
1481FK6K	\$319.00	6.00 [152]	24.00 x 5.00 x 6.00 [610 x 127 x 152]	PDF
1481FK8K	\$326.00	8.00 [203]	24.00 x 8.00 x 8.00 [610 x 203 x 203]	PDF
1481FG16K	\$344.00	16.00 [406]	18.00 x 10.00 x 16.00 [457 x 254 x 406]	PDF
1481FK12K	\$360.00	12.00 [305]	24.00 x 10.00 x 12.00 [610 x 254 x 305]	PDF
1481FK16K	\$393.00	16.00 [406]	24.00 x 12.00 x 16.00 [610 x 305 x 406]	PDF

Note: Dimensions in inches [millimeters].

