

Enclosure Accessories



Gasket Kits



NEMA 12 Enclosures

- Self-adhesive cellular neoprene gasket for NEMA 12 enclosures.
- Supplied in 10 ft [3 m] rolls, 0.19 x 0.75in [4.83 x 19.1mm].

NEMA 4 and 4X Enclosures

- Self-adhesive neoprene blend gasket for NEMA 4 and 4X enclosures.
- Supplied in 10 ft [3 m] rolls, 0.25 x 0.75in [6.35 x 19.1mm].

Gasket Kits			
Part Number	Price	Material	For NEMA Type
<u>1481DJ10</u>	\$14.50	NEMA 12	neoprene
<u>1481DJN410</u>	\$23.00	NEMA 4/4X	neoprene/EPDM/ SBR

Folding Shelf



Application

- Supports various equipment used temporarily to service/program switchgear inside enclosures.
- Mounts with bolts through doors or sides.
- Supports up to 100-lb weight capacity.
- Stainless steel or powder coat finish.

ANSI 61 Gray Folding Shelf			
Part Number	Price	Work Surface	Drawing Link
<u>FDS1212GY</u>	\$181.00	12.00 x 12.00 [305 x 305]	<u>PDF</u>
<u>FDS1818GY</u>	\$227.00	18.00 x 18.00 [457 x 457]	<u>PDF</u>
<u>FDS2424GY</u>	\$253.00	24.00 x 24.00 [610 x 610]	<u>PDF</u>
Note: Dimensions in inches [millimeters].			

RAL7035 Light Gray Folding Shelf			
Part Number	Price	Work Surface	Drawing Link
<u>FDS1212LG</u>	\$181.00	12.00 x 12.00 [305 x 305]	—
<u>FDS1818LG</u>	\$227.00	18.00 x 18.00 [457 x 457]	—
<u>FDS2424LG</u>	\$253.00	24.00 x 24.00 [610 x 610]	<u>PDF</u>
Note: Dimensions in inches [millimeters].			

316 Stainless Steel Folding Shelf			
Part Number	Price	Work Surface	Drawing Link
<u>FDS1212S16</u>	\$792.00	12.00 x 12.00 [305 x 305]	<u>PDF</u>
<u>FDS1818S16</u>	\$1,046.00	18.00 x 18.00 [457 x 457]	<u>PDF</u>
<u>FDS2424S16</u>	\$1,153.00	24.00 x 24.00 [610 x 610]	<u>PDF</u>
Note: Dimensions in inches [millimeters].			