

Fan Heaters with Thermostat



Features

- Designed to prevent condensation or maintain minimum temperature in enclosures.
- Built in Thermostat. (-18° C to +38° C) (0° F to +100° F).
- Fan Auto/On switch with pilot light for Heat On indication.
- High temperature safety protection.
- Aluminum alloy outer casing.
- Connection via terminal block.
- 1300W models are cURus approved only.

Listings

- UL File E331157
- CSA File LR43697



Fan Heaters with Thermostat						
Part Number	Price	Watts	Voltage	Hz	CFM	Drawing Link
FLHTF125A115	\$304.00	125W	120 VAC	60 Hz	20	PDF
FLHTF200A115	\$361.00	200W	120 VAC	60 Hz		PDF
FLHTF400A115	\$418.00	400W	120 VAC	60 Hz		PDF
FLHTF800A115	\$475.00	800W	120 VAC	60 Hz		PDF
FLHTF1300A115	\$502.00	1300W	120 VAC	60 Hz	50	PDF
FLHTF125A230	\$304.00	105/125W	220-240 VAC	50/60 Hz	20	PDF
FLHTF200A230	\$361.00	165/200W	220-240 VAC	50/60 Hz		PDF
FLHTF400A230	\$418.00	335/400W	220-240 VAC	50/60 Hz		PDF
FLHTF800A230	\$475.00	670/800W	220-240 VAC	50/60 Hz		PDF
FLHTF1300A230	\$502.00	1080/1300W	220-240 VAC	50/60 Hz	50	PDF