

# Eclipse Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Floor-Mount



## Applications

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

## Construction

- Formed 12-gauge 304 or 316 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- Body stiffeners are provided in the larger enclosures for extra rigidity.
- Heavy duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Center post is removable for easy installation of the subpanel.
- Formed lip on door and top of enclosure opening exclude flowing liquids and contaminants.
- Continuously hinged doors may be removed by pulling the stainless steel hinge pin.
- Doors are secured with heavy duty stainless steel clamps.
- Provision for padlocking.
- 12 in [305 mm] floor stands are welded to the enclosure.
- Seamless poured-in-place gasket.
- Panel supports are provided for easy panel installation.
- Collar studs are provided for mounting subpanels.
- A bonding stud is provided on the door, and a grounding stud is provided in the enclosure for each door.
- A literature pocket is provided.

## Finish

- Cover and enclosure are natural stainless steel with a #4 smooth brushed finish.
- Removable 10-gauge subpanel is finished in RAL9003 white powder coating.

## Listings

- UL 508A Type 3R, 4, 4X, and 12 [UL File E65324]
- CSA Type 3R, 4, 4X, and 12 [CSA File LR21001]
- Complies with
  - NEMA Type 3R, 4, 4X, 12, and 13
  - IEC 60529, IP66



Eclipse Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Floor-Mount						
304 Stainless Steel	Price	316 Stainless Steel	Price	Enclosure Size HxWxD	Subpanel Size HxW	Drawing Link
<a href="#">1422N4SSB12F</a>	\$6,226.00	<a href="#">1422N4S16B12F</a>	\$7,213.00	60.13 x 48.06 x 13.88 [1527 x 1221 x 353]	56.00 x 44.00 [1422 x 1118]	<a href="#">PDF</a>
<a href="#">1422N4SSD12F</a>	\$7,037.00	<a href="#">1422N4S16D12F</a>	\$8,130.00	60.13 x 60.06 x 13.88 [1527 x 1526 x 353]	56.00 x 56.00 [1422 x 1422]	<a href="#">PDF</a>
<a href="#">1422N4SSE12F</a>	\$8,371.00	<a href="#">1422N4S16E12F</a>	\$9,705.00	72.13 x 60.06 x 13.88 [1832 x 1526 x 353]	68.00 x 56.00 [1727 x 1422]	<a href="#">PDF</a>
<a href="#">1422N4SSF12F</a>	\$8,787.00	<a href="#">1422N4S16F12F</a>	\$10,141.00	72.13 x 72.06 x 13.88 [1832 x 1830 x 353]	68.00 x 68.00 [1727 x 1727]	<a href="#">PDF</a>
<a href="#">1422N4SSF24F</a>	\$10,927.00	<a href="#">1422N4S16F24F</a>	\$12,646.00	72.13 x 72.06 x 25.88 [1832 x 1830 x 657]	68.00 x 68.00 [1727 x 1727]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# Eclipse Series NEMA 3R, 4, 4X, 12, and 13 Stainless Steel Two-Door Floor-Mount



## Dimensions

