

Enclosure Accessories

Frameless Window Kits



Application

- Designed for indoor use on NEMA 12 and 13 enclosures.
- Scratch-resistant polycarbonate window is 0.25 in [6.35 mm] thick.
- Double-sided tape is on the window for easy installation.
- Mounting hardware and template are included.

Frameless Window Kits				
Part Number	Price	Window Dimensions AxB	Maximum Cut-Out Size	Drawing Link
1481WFL52	\$59.00	5.50 x 3.00 [140 x 76]		PDF
1481WFL133	\$73.00	13.88 x 3.88 [353 x 99]		PDF
1481WFL96	\$81.00	9.62 x 7.19 [244 x 183]		PDF

Note: Dimensions in inches [millimeters].

