

NEMA 1, 4, and 12 Wiring Trough



Designed to enclose and protect multiple wiring junctions from dirt, dust, oil, and water.

Construction

- Formed 14-gauge steel.
- Smooth continuously welded seams.
- Butt-hinged cover is secured with easily operated screw clamps.
- Oil resistant gaskets are permanently secured.
- 12-gauge external mounting feet are welded to the back.
- Troughs and covers are finished in ANSI 61 gray powder coating.

Listings

- UL 870 Type 1, 4, and 12 [File E186830]
- CSA Type 1, 4, and 12 [File LL21312]
- Complies with:
 - NEMA Type 1, 4, and 12
 - IEC 60529, IP54



NEMA 1, 4, and 12 Wiring Trough			
Part Number	Price	Overall Size HxWxD	Drawing Link
1486B12	\$133.00	2.50 x 2.50 x 12.00 [64 x 64 x 305]	PDF
1486B18	\$143.00	2.50 x 2.50 x 18.00 [64 x 64 x 457]	PDF
1486B24	\$153.00	2.50 x 2.50 x 24.00 [64 x 64 x 610]	PDF
1486B30	\$165.00	2.50 x 2.50 x 30.00 [64 x 64 x 762]	PDF
1486B36	\$174.00	2.50 x 2.50 x 36.00 [64 x 64 x 914]	PDF
1486B48	\$194.00	2.50 x 2.50 x 48.00 [64 x 64 x 1219]	PDF
1486B60	\$215.00	2.50 x 2.50 x 60.00 [64 x 64 x 1524]	PDF
1486B72	\$234.00	2.50 x 2.50 x 72.00 [64 x 64 x 1829]	PDF
1486C12	\$155.00	4.00 x 4.00 x 12.00 [102 x 102 x 305]	PDF
1486C18	\$174.00	4.00 x 4.00 x 18.00 [102 x 102 x 457]	PDF
1486C24	\$194.00	4.00 x 4.00 x 24.00 [102 x 102 x 610]	PDF
1486C30	\$213.00	4.00 x 4.00 x 30.00 [102 x 102 x 762]	PDF
1486C36	\$232.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	PDF
1486C48	\$280.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	PDF
1486C60	\$318.00	4.00 x 4.00 x 60.00 [102 x 102 x 1524]	PDF
1486C72	\$348.00	4.00 x 4.00 x 72.00 [102 x 102 x 1829]	PDF
1486D12	\$183.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	PDF
1486D18	\$211.00	6.00 x 6.00 x 18.00 [152 x 152 x 457]	PDF
1486D24	\$240.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	PDF
1486D30	\$268.00	6.00 x 6.00 x 30.00 [152 x 152 x 762]	PDF
1486D36	\$298.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	PDF
1486D48	\$355.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	PDF
1486D60	\$427.00	6.00 x 6.00 x 60.00 [152 x 152 x 1524]	PDF
1486D72	\$487.00	6.00 x 6.00 x 72.00 [152 x 152 x 1829]	PDF
1486E12	\$219.00	8.00 x 8.00 x 12.00 [203 x 203 x 305]	PDF
1486E24	\$289.00	8.00 x 8.00 x 24.00 [203 x 203 x 610]	PDF
1486E36	\$369.00	8.00 x 8.00 x 36.00 [203 x 203 x 914]	PDF
1486E48	\$458.00	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	PDF
1486E60	\$538.00	8.00 x 8.00 x 60.00 [203 x 203 x 1524]	PDF
1486G24	\$400.00	12.00 x 12.00 x 24.00 [305 x 305 x 610]	PDF
1486G36	\$516.00	12.00 x 12.00 x 36.00 [305 x 305 x 914]	PDF
1486G48	\$651.00	12.00 x 12.00 x 48.00 [305 x 305 x 1219]	PDF
1486G60	\$751.00	12.00 x 12.00 x 60.00 [305 x 305 x 1524]	PDF

Note: Dimensions in inches [millimeters].