

19-inch Rack Mount Clamping Shelf



Description

This shelf has been designed to provide superior ventilation for cable and satellite boxes and other components that generate considerable heat. Features two adjustable foam padded mounting bars to secure components without fear of scratches.

19-inch Rack Mount Clamping Shelf			
Part Number	Price	Rack Units	Drawing Link
RACSV190315BK1	\$111.00	2U	PDF
RACSV190515BK1	\$121.00	3U	PDF
RACSV190715BK1	\$117.00	4U	PDF
Note: Dimensions in inches [millimeters].			

Features

- Allows easy rack mounting of narrow equipment or items that do not have rack mounting capabilities.
- Includes two adjustable, gasketed (to protect from scratching the clamped equipment), horizontal clamps.
- Designed for equipment requiring front adjustment without sliding around the shelf.
- Choice of four clamp locations depending on depth of equipment.
- Choice of three shelf heights.
- Mounted equipment height should be at least 0.5in [12.7mm] shorter than shelf panel height to allow clearance for the gasketed clamps.
- Provides a sturdy shelf without obstructing upward heat movement.
- Rear lip folded up for extra strength and doubles as an equipment retainer.
- 14-gauge steel construction.
- Tested to nearly double the suggested load rating of 200 lb [91 kg].
- Black powder coat finish.

Listings

- TAA compliant for GSA Schedule purchases.

