

19-Inch Rack Mount Locking Storage Drawer



Features

- Constructed of 14- and 16-gauge steel.
- Includes front plastic pull handle locking mechanism.
- Inside of drawer width is 16.12in [411 mm] wide.
- Complete drawer with slides, hardware, lock and two keys.
- Available in three depths.
- Rear support brackets included for all depths or can be supported from rear accessory rail.
- 6-pack of 10-32 rack screws are included.
- Finished in textured powder coat.
- Tested to nearly double the suggested load rating of 145 lb [66 kg] when mounted to two-pair/4-post rack rails.
- Rated for 60 lb [27 kg] when mounted one-pair/two-post rack rails.



Listings

- TAA compliant for GSA Schedule purchases.

19-Inch Rack Mount Locking Storage Drawer					
Black	RAL7035 Gray	Price	Rack Units	Depth	Drawing Link
<u>RDRW1900312BK1</u>	<u>RDRW1900312LG1</u>	\$239.00	2U	12.25 [311]	<u>PDF</u>
<u>RDRW1900316BK1</u>	<u>RDRW1900316LG1</u>	\$254.00	2U	16.25 [413]	<u>PDF</u>
<u>RDRW1900322BK1</u>	<u>RDRW1900322LG1</u>	\$262.00	2U	22.25 [565]	<u>PDF</u>
<u>RDRW1900512BK1</u>	<u>RDRW1900512LG1</u>	\$290.00	3U	12.25 [311]	<u>PDF</u>
<u>RDRW1900516BK1</u>	<u>RDRW1900516LG1</u>	\$295.00	3U	16.25 [413]	<u>PDF</u>
<u>RDRW1900522BK1</u>	<u>RDRW1900522LG1</u>	\$310.00	3U	22.25 [565]	<u>PDF</u>
<u>RDRW1900712BK1</u>	<u>RDRW1900712LG1</u>	\$290.00	4U	12.25 [311]	<u>PDF</u>
<u>RDRW1900716BK1</u>	<u>RDRW1900716LG1</u>	\$302.00	4U	16.25 [413]	<u>PDF</u>
<u>RDRW1900722BK1</u>	<u>RDRW1900722LG1</u>	\$336.00	4U	22.25 [565]	<u>PDF</u>
<u>RDRW1900822BK1</u>	<u>RDRW1900822LG1</u>	\$363.00	5U	22.25 [565]	<u>PDF</u>
<u>RDRW1901222BK1</u>	<u>RDRW1901222LG1</u>	\$414.00	7U	22.25 [565]	<u>PDF</u>
Note: Dimensions in inches [millimeters].					