

Two-Post Centered Shelf



Features

- 16-gauge steel construction.
- The vented version provides a sturdy shelf without obstructing upward heat movement.
- Front and rear lip folded for extra strength and to contain equipment.
- Rugged textured black powder coat finish.
- Solid version available in either 19 in [483 mm] or 23 in [584 mm] rack panel width.
- Tested to nearly double the suggested load rating of 200 lb [91 kg].
- Finished in textured black powder coat.



Listings

- TAA compliant for GSA Schedule purchases.

Solid Two Post Centered Shelf					
Part Number	Price	Rack Units	Rack Width	Shelf Depth	Drawing Link
DNDMS1916BK1	\$99.00	2U	19.0 [483]	16.00 [406]	PDF
DNDMS1918BK1	\$102.00	2U	19.0 [483]	18.00 [457]	PDF
DNDMS1920BK1	\$105.00	2U	19.0 [483]	20.00 [508]	PDF
DNDMS1922BK1	\$107.00	2U	19.0 [483]	22.00 [559]	PDF
DNDMS1924BK1	\$110.00	2U	19.0 [483]	24.00 [610]	PDF
DNDMS19BK1	\$99.00	2U	19.0 [483]	19.50 [495]	PDF
DNDMS23BK1	\$110.00	2U	23.0 [584]	19.50 [495]	PDF
Note: Dimensions in inches [millimeters].					

Vented Two Post Centered Shelf					
Part Number	Price	Rack Units	Rack Width	Shelf Depth	Drawing Link
DNDMV1918BK1	\$102.00	2U	19.0 [483]	18.00 [457]	PDF
DNDMV19BK1	\$105.00	2U	19.0 [483]	19.50 [495]	PDF
Note: Dimensions in inches [millimeters].					