

Two-Post Extension Support Bracket



Description

The RDAB is similar to a 2U shelf but allows the rack equipment to be positioned in the center of the rack. This helps stabilize the rack while using less space than having equipment mounted behind.

Features

- Ideal for mounting a UPS, server, switch, NVR and other rack mount equipment.
- Mounts to the front and/or rear of the rack for maximum load rating.
- Available in four depths.
- Angles mount to 19 in [483 mm], 23 in [584 mm] and 24 in [610 mm]
- Includes all four pieces shown as well as mounting hardware.

Construction

- Constructed from 14-gauge steel.
- Smooth black powder coat
- Tested to nearly double the suggested load rating of 400 lb [181 kg].

Listings

- TAA compliant
- EIA compliant



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

Two-Post Extension Support Bracket

Part Number	Price	Rack Units	Overall Size HxD	Drawing Link
RDAB2U15	\$54.00	2U	3.50 x 6.00 [89 x 152]	PDF
RDAB2U20	\$59.00	2U	3.50 x 8.50 [89 x 216]	PDF
RDAB2U26	\$62.00	2U	3.50 x 11.50 [89 x 292]	PDF
RDAB2U31	\$66.00	2U	3.50 x 14.00 [89 x 356]	PDF

Note: Dimensions in inches [millimeters].