

Adjustable Depth Wall-Mount 19-Inch Rack with Shelf



Features

- Available in 4U and 8U mounting heights.
 - Includes 3.5 in [89mm] (2U) of space for non-rack mounting equipment.
- Includes twelve 12 in [305 mm] [305 mm] deep accessory shelf.
- Depth is adjustable from 12 in [305 mm] [305 mm] to 18 in [457 mm] with ease so there is no need to disassemble the whole rack to adjust the depth.
- Rear cable access with multiple tie points for cable management.
- Knockdown design ships unassembled for easy handling, reduced freight cost and shipping protection.

Construction

- Constructed from 14-gauge steel.
- Tapped 10-32 19 in [483 mm] mounting rails are constructed from 14-gauge steel and include rack unit indicators.
- SCREW1032-25, 25-pack of 10-32 mounting hardware included.
- Load rated for up to 100 lb [45 kg].
- Finished in smooth black powder coat.

Listings

- TAA compliant for GSA Schedule purchases.
- RoHS



Adjustable Depth Wall-Mount 19-Inch Rack with Shelf			
Part Number	Price	Rack Units	Drawing Link
APBS194UBK	\$146.00	4U	PDF
APBS198UBK	\$212.00	8U	PDF