

Aluminum Panels for 19-Inch Racks



Application

Install in unused 19 in [483 mm] wide rack space to improve both cooling efficiency and prevent air recirculation.

Features

- Fits standard EIA compliant rails.

Construction

- Constructed of 8-gauge (0.125 in [3mm]) 5052-H32 aluminum.
- Finished in smooth powder coat paint or unfinished.

Listings

- TAA compliant for GSA Schedule purchases.
- RoHS



Aluminum Panels for 19-Inch Racks

<i>Gloss Black</i>	<i>Matte Black</i>	<i>RAL7035 Gray</i>	<i>ANSI 61 Gray</i>	<i>Unfinished</i>	<i>Price</i>	<i>Rack Units</i>	<i>Panel Height</i>	<i>Drawing Link</i>
<u>PBPA19001BK2</u>	<u>PBPA19001BK</u>	<u>PBPA19001LG2</u>	<u>PBPA19001GY2</u>	<u>PBPA19001UNF</u>	\$12.50	1U	1.75 [44]	<u>PDF</u>
<u>PBPA19003BK2</u>	<u>PBPA19003BK</u>	<u>PBPA19003LG2</u>	<u>PBPA19003GY2</u>	<u>PBPA19003UNF</u>	\$18.25	2U	3.50 [89]	<u>PDF</u>
<u>PBPA19005BK2</u>	<u>PBPA19005BK</u>	<u>PBPA19005LG2</u>	<u>PBPA19005GY2</u>	<u>PBPA19005UNF</u>	\$27.50	3U	5.25 [133]	<u>PDF</u>
<u>PBPA19007BK2</u>	<u>PBPA19007BK</u>	<u>PBPA19007LG2</u>	<u>PBPA19007GY2</u>	<u>PBPA19007UNF</u>	\$32.50	4U	7.00 [178]	<u>PDF</u>
<u>PBPA19008BK2</u>	—	<u>PBPA19008LG2</u>	<u>PBPA19008GY2</u>	<u>PBPA19008UNF</u>	\$38.50	5U	8.75 [222]	<u>PDF</u>
<u>PBPA19010BK2</u>	—	<u>PBPA19010LG2</u>	<u>PBPA19010GY2</u>	<u>PBPA19010UNF</u>	\$45.00	6U	10.50 [267]	<u>PDF</u>
<u>PBPA19012BK2</u>	—	<u>PBPA19012LG2</u>	<u>PBPA19012GY2</u>	<u>PBPA19012UNF</u>	\$54.00	7U	12.25 [311]	<u>PDF</u>
<u>PBPA19014BK2</u>	—	<u>PBPA19014LG2</u>	<u>PBPA19014GY2</u>	<u>PBPA19014UNF</u>	\$61.00	8U	14.00 [356]	<u>PDF</u>
<u>PBPA19015BK2</u>	—	<u>PBPA19015LG2</u>	<u>PBPA19015GY2</u>	<u>PBPA19015UNF</u>	\$66.00	9U	15.75 [400]	<u>PDF</u>
<u>PBPA19017BK2</u>	—	<u>PBPA19017LG2</u>	<u>PBPA19017GY2</u>	<u>PBPA19017UNF</u>	\$73.00	10U	17.50 [445]	<u>PDF</u>

Note: Dimensions in inches [millimeters].