

# Aluminum Panels for 19-Inch Racks



## Application

Install in unused 19 in [483 mm] wide rack space to improve both cooling efficiency and prevent air recirculation.

## Features

- Fits standard EIA compliant rails.

## Construction

- Constructed of 8-gauge (0.125 in [3mm]) 5052-H32 aluminum.
- Finished in smooth powder coat paint or unfinished.

## Listings

- TAA compliant for GSA Schedule purchases.
- RoHS



**Aluminum Panels for 19-Inch Racks**

| <i>Gloss Black</i>                  | <i>Matte Black</i>                 | <i>RAL7035 Gray</i>                 | <i>ANSI 61 Gray</i>                 | <i>Unfinished</i>                   | <i>Price</i> | <i>Rack Units</i> | <i>Panel Height</i> | <i>Drawing Link</i>        |
|-------------------------------------|------------------------------------|-------------------------------------|-------------------------------------|-------------------------------------|--------------|-------------------|---------------------|----------------------------|
| <a href="#"><u>PBPA19001BK2</u></a> | <a href="#"><u>PBPA19001BK</u></a> | <a href="#"><u>PBPA19001LG2</u></a> | <a href="#"><u>PBPA19001GY2</u></a> | <a href="#"><u>PBPA19001UNF</u></a> | \$12.50      | 1U                | 1.75 [44]           | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>PBPA19003BK2</u></a> | <a href="#"><u>PBPA19003BK</u></a> | <a href="#"><u>PBPA19003LG2</u></a> | <a href="#"><u>PBPA19003GY2</u></a> | <a href="#"><u>PBPA19003UNF</u></a> | \$18.25      | 2U                | 3.50 [89]           | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>PBPA19005BK2</u></a> | <a href="#"><u>PBPA19005BK</u></a> | <a href="#"><u>PBPA19005LG2</u></a> | <a href="#"><u>PBPA19005GY2</u></a> | <a href="#"><u>PBPA19005UNF</u></a> | \$27.50      | 3U                | 5.25 [133]          | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>PBPA19007BK2</u></a> | <a href="#"><u>PBPA19007BK</u></a> | <a href="#"><u>PBPA19007LG2</u></a> | <a href="#"><u>PBPA19007GY2</u></a> | <a href="#"><u>PBPA19007UNF</u></a> | \$32.50      | 4U                | 7.00 [178]          | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>PBPA19008BK2</u></a> | —                                  | <a href="#"><u>PBPA19008LG2</u></a> | <a href="#"><u>PBPA19008GY2</u></a> | <a href="#"><u>PBPA19008UNF</u></a> | \$38.50      | 5U                | 8.75 [222]          | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>PBPA19010BK2</u></a> | —                                  | <a href="#"><u>PBPA19010LG2</u></a> | <a href="#"><u>PBPA19010GY2</u></a> | <a href="#"><u>PBPA19010UNF</u></a> | \$45.00      | 6U                | 10.50 [267]         | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>PBPA19012BK2</u></a> | —                                  | <a href="#"><u>PBPA19012LG2</u></a> | <a href="#"><u>PBPA19012GY2</u></a> | <a href="#"><u>PBPA19012UNF</u></a> | \$54.00      | 7U                | 12.25 [311]         | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>PBPA19014BK2</u></a> | —                                  | <a href="#"><u>PBPA19014LG2</u></a> | <a href="#"><u>PBPA19014GY2</u></a> | <a href="#"><u>PBPA19014UNF</u></a> | \$61.00      | 8U                | 14.00 [356]         | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>PBPA19015BK2</u></a> | —                                  | <a href="#"><u>PBPA19015LG2</u></a> | <a href="#"><u>PBPA19015GY2</u></a> | <a href="#"><u>PBPA19015UNF</u></a> | \$66.00      | 9U                | 15.75 [400]         | <a href="#"><u>PDF</u></a> |
| <a href="#"><u>PBPA19017BK2</u></a> | —                                  | <a href="#"><u>PBPA19017LG2</u></a> | <a href="#"><u>PBPA19017GY2</u></a> | <a href="#"><u>PBPA19017UNF</u></a> | \$73.00      | 10U               | 17.50 [445]         | <a href="#"><u>PDF</u></a> |

Note: Dimensions in inches [millimeters].