

Universal Rack Shelf



Features

- Constructed of 14- or 16-gauge steel.
- Universal design mounts to any standard EIA compliant rack or cabinet.
- Allows easy rack mounting of equipment or items that do not have rack mounting capabilities.
- Mounts to rack rails either as an internal shelf or external shelf/work area.
- Available in either vented or solid versions.
- Rugged textured black powder coat finish.



Solid Universal Rack Shelf					
Part Number	Price	Rack Units	Rack Width	Shelf Depth	Drawing Link
RASU190107DBK1	\$44.00	1U	19.0 [483]	7.00 [178]	PDF
RASU190107UBK1	\$44.00	1U	19.0 [483]	7.00 [178]	PDF
RASU190110BK1	\$49.00	1U	19.0 [483]	10.00 [254]	PDF
RASU190112BK1	\$52.00	1U	19.0 [483]	12.00 [305]	PDF
RASU190115BK1	\$61.00	1U	19.0 [483]	15.00 [381]	PDF
RASU190120BK1	\$64.00	1U	19.0 [483]	20.00 [508]	PDF
RASU190312BK1	\$57.00	2U	19.0 [483]	12.00 [305]	PDF
RASU190315BK1	\$62.00	2U	19.0 [483]	15.00 [381]	PDF
RASU190318BK1	\$67.00	2U	19.0 [483]	18.00 [457]	PDF
RASU190320BK1	\$72.00	2U	19.0 [483]	20.00 [508]	PDF
RASU190515BK1	\$64.00	3U	19.0 [483]	15.00 [381]	PDF
RASU230515BK1	\$74.00	3U	19.0 [483]	15.00 [381]	PDF
RASU190715BK1	\$82.00	4U	19.0 [483]	15.00 [381]	PDF
RASU190520BK1	\$78.00	3U	19.0 [483]	20.00 [508]	PDF
RASU190522BK1	\$84.00	3U	19.0 [483]	22.00 [559]	PDF
RASU190524BK1	\$88.00	3U	19.0 [483]	24.00 [610]	PDF
RASU190720BK1	\$93.00	4U	23.0 [584]	20.00 [508]	PDF
RASU230520BK1	\$90.00	3U	23.0 [584]	20.00 [508]	PDF

Note: Dimensions in inches [millimeters].

Vented Universal Rack Shelf					
Part Number	Price	Rack Units	Rack Width	Shelf Depth	Drawing Link
RASV190107DBK1	\$50.00	1U	19.0 [483]	7.00 [178]	PDF
RASV190107UBK1	\$50.00	1U	19.0 [483]	7.00 [178]	PDF
RASV190110BK1	\$57.00	1U	19.0 [483]	10.00 [254]	PDF
RASV190112BK1	\$61.00	1U	19.0 [483]	12.00 [305]	PDF
RASV190115BK1	\$64.00	1U	19.0 [483]	15.00 [381]	PDF
RASV190120BK1	\$67.00	1U	19.0 [483]	20.00 [508]	PDF
RASV190312BK1	\$66.00	2U	19.0 [483]	12.00 [305]	PDF
RASV190315BK1	\$70.00	2U	19.0 [483]	15.00 [381]	PDF
RASV190318BK1	\$72.00	2U	19.0 [483]	18.00 [457]	PDF
RASV190320BK1	\$74.00	2U	19.0 [483]	20.00 [508]	PDF
RASV190515BK1	\$67.00	3U	19.0 [483]	15.00 [381]	PDF
RASV190520BK1	\$74.00	3U	19.0 [483]	20.00 [508]	PDF
RASV190715BK1	\$74.00	4U	19.0 [483]	15.00 [381]	PDF
RASV190720BK1	\$77.00	4U	19.0 [483]	20.00 [508]	PDF
RASV230515BK1	\$90.00	3U	23.0 [584]	15.00 [381]	PDF
RASV230520BK1	\$99.00	3U	23.0 [584]	20.00 [508]	PDF

Note: Dimensions in inches [millimeters].