

NEMA 12 and 13 Pushbutton Operator Console



Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Ideal for wall or surface mounting to provide the necessary control slope.
- Provides protection from dirt, dust, oil, and water.

Construction

- Formed 14-gauge steel.
- Smooth continuously welded seams.
- Construction provides either a 30° or 60° slope on front cover depending on mounting position.
- Welded brackets provide for enclosure mounting.
- Captive cover screws thread into sealed wells.
- Larger enclosures provide internally hinged removable covers designed to hold the cover open during wiring (as noted in table).
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray powder coating.

Listings

- UL 508A Type 12 and 13 [UL File E65324]
- CSA Type 12 and 13 [CSA File LR21001]
- Complies with
 - NEMA Type 12 and 13
 - IEC 60529, IP54
- All appropriate components are required to maintain these standards.



NEMA 12 and 13 Pushbutton Operator Console							
22 mm	Price	30 mm	Price	Console Size HxWxD	Drawing Link	# Holes	Hinged
1490MD1	\$91.00	1490D1	\$94.00	3.53 x 3.56 x 5.06 [90 x 90 x 129]	PDF	1	No
1490MD2	\$106.00	1490D2	\$111.00	3.53 x 5.81 x 5.06 [90 x 148 x 129]	PDF	2	
1490MD3	\$122.00	1490D3	\$126.00	3.53 x 8.06 x 5.06 [90 x 205 x 129]	PDF	3	
1490MD4	\$136.00	1490D4	\$141.00	3.53 x 10.31 x 5.06 [90 x 262 x 129]	PDF	4	
1490MG4	\$153.00	1490G4	\$157.00	6.78 x 6.56 x 6.94 [172 x 167 x 176]	PDF	4	Yes
1490MG6	\$176.00	1490G6	\$182.00	6.78 x 8.81 x 6.94 [172 x 224 x 176]	PDF	6	
1490MG8	\$199.00	1490G8	\$206.00	6.78 x 11.06 x 6.94 [172 x 281 x 176]	PDF	8	
1490MH9	\$209.00	1490H9	\$215.00	8.75 x 8.81 x 8.06 [222 x 224 x 205]	PDF	9	
1490MG10	\$222.00	1490G10	\$227.00	6.78 x 13.31 x 6.94 [172 x 338 x 176]	PDF	10	
1490MJ12	\$233.00	1490G12	\$250.00	6.78 x 15.56 x 6.94 [172 x 395 x 176]	PDF	12	
1490MG12	\$243.00	1490J12	\$238.00	10.69 x 8.81 x 9.19 [272 x 224 x 233]	PDF	12	
1490MJ16	\$258.00	1490G16	\$289.00	6.78 x 20.06 x 6.94 [172 x 510 x 176]	PDF	16	
1490MG16	\$281.00	1490J16	\$265.00	10.69 x 11.06 x 9.19 [272 x 281 x 233]	PDF	16	
1490MJ20	\$298.00	1490J20	\$306.00	10.69 x 13.31 x 9.19 [272 x 338 x 233]	PDF	20	
1490MK25	\$336.00	1490K25	\$348.00	12.63 x 13.31 x 10.31 [321 x 338 x 262]	PDF	25	
1490MK30	\$367.00	1490K30	\$380.00	12.63 x 15.56 x 10.31 [321 x 395 x 262]	PDF	30	

Note: Dimensions in inches [millimeters].

NEMA 12 and 13 Pushbutton Operator Consolelet



Dimensions

