

NEMA 12 and 13 Pushbutton Operator Console



Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Ideal for wall or surface mounting to provide the necessary control slope.
- Provides protection from dirt, dust, oil, and water.

Construction

- Formed 14-gauge steel.
- Smooth continuously welded seams.
- Construction provides either a 30° or 60° slope on front cover depending on mounting position.
- Welded brackets provide for enclosure mounting.
- Captive cover screws thread into sealed wells.
- Larger enclosures provide internally hinged removable covers designed to hold the cover open during wiring (as noted in table).
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray powder coating.

Listings

- UL 508A Type 12 and 13 [UL File E65324]
- CSA Type 12 and 13 [CSA File LR21001]
- Complies with
 - NEMA Type 12 and 13
 - IEC 60529, IP54
- All appropriate components are required to maintain these standards.



| NEMA 12 and 13 Pushbutton Operator Console | | | | | | | |
|--|----------|-------------------------|----------|---|---------------------|---------|--------|
| 22 mm | Price | 30 mm | Price | Console Size HxWxD | Drawing Link | # Holes | Hinged |
| 1490MD1 | \$91.00 | 1490D1 | \$94.00 | 3.53 x 3.56 x 5.06 [90 x 90 x 129] | PDF | 1 | No |
| 1490MD2 | \$106.00 | 1490D2 | \$111.00 | 3.53 x 5.81 x 5.06 [90 x 148 x 129] | PDF | 2 | |
| 1490MD3 | \$122.00 | 1490D3 | \$126.00 | 3.53 x 8.06 x 5.06 [90 x 205 x 129] | PDF | 3 | |
| 1490MD4 | \$136.00 | 1490D4 | \$141.00 | 3.53 x 10.31 x 5.06 [90 x 262 x 129] | PDF | 4 | |
| 1490MG4 | \$153.00 | 1490G4 | \$157.00 | 6.78 x 6.56 x 6.94 [172 x 167 x 176] | PDF | 4 | Yes |
| 1490MG6 | \$176.00 | 1490G6 | \$182.00 | 6.78 x 8.81 x 6.94 [172 x 224 x 176] | PDF | 6 | |
| 1490MG8 | \$199.00 | 1490G8 | \$206.00 | 6.78 x 11.06 x 6.94 [172 x 281 x 176] | PDF | 8 | |
| 1490MH9 | \$209.00 | 1490H9 | \$215.00 | 8.75 x 8.81 x 8.06 [222 x 224 x 205] | PDF | 9 | |
| 1490MG10 | \$222.00 | 1490G10 | \$227.00 | 6.78 x 13.31 x 6.94 [172 x 338 x 176] | PDF | 10 | |
| 1490MJ12 | \$233.00 | 1490G12 | \$250.00 | 6.78 x 15.56 x 6.94 [172 x 395 x 176] | PDF | 12 | |
| 1490MG12 | \$243.00 | 1490J12 | \$238.00 | 10.69 x 8.81 x 9.19 [272 x 224 x 233] | PDF | 12 | |
| 1490MJ16 | \$258.00 | 1490G16 | \$289.00 | 6.78 x 20.06 x 6.94 [172 x 510 x 176] | PDF | 16 | |
| 1490MG16 | \$281.00 | 1490J16 | \$265.00 | 10.69 x 11.06 x 9.19 [272 x 281 x 233] | PDF | 16 | |
| 1490MJ20 | \$298.00 | 1490J20 | \$306.00 | 10.69 x 13.31 x 9.19 [272 x 338 x 233] | PDF | 20 | |
| 1490MK25 | \$336.00 | 1490K25 | \$348.00 | 12.63 x 13.31 x 10.31 [321 x 338 x 262] | PDF | 25 | |
| 1490MK30 | \$367.00 | 1490K30 | \$380.00 | 12.63 x 15.56 x 10.31 [321 x 395 x 262] | PDF | 30 | |

Note: Dimensions in inches [millimeters].

NEMA 12 and 13 Pushbutton Operator Consolelet



Dimensions

