

NEMA 12 and 13 Extra Deep Pushbutton



Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil, and water.

Construction

- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Captive cover screws fasten into threaded, sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring (see drawings).
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray powder coating.

Listings

- UL 508A Type 12 and 13 [UL File E65324]
- CSA Type 12 and 13 [CSA File LR21001]
- Complies with
 - NEMA Type 12 and 13
 - IEC 60529, IP54
- All appropriate components are required to maintain these standards.



NEMA 12 and 13 Extra Deep Pushbutton								
22 mm	Price	30 mm	Price	Size HxWxD	Drawing Link	# Holes	Steel Gauge	Hinged
1437MA	\$88.00	1437A	\$91.00	4.31 x 4.31 x 4.91 [109 x 109 x 125]	PDF	1	16	No
1437MB	\$102.00	1437B	\$105.00	6.31 x 4.31 x 4.97 [160 x 109 x 126]	PDF	2	14	Yes
1437MC	\$116.00	1437C	\$118.00	8.31 x 4.31 x 4.97 [211 x 109 x 126]	PDF	3		
1437MD	\$129.00	1437D	\$131.00	10.31 x 4.31 x 4.97 [262 x 109 x 126]	PDF	4		
1437MF	\$130.00	1437F	\$134.00	7.56 x 6.56 x 4.97 [192 x 167 x 126]	PDF	4		
1437MH	\$148.00	1437H	\$152.00	9.81 x 6.56 x 4.97 [249 x 167 x 126]	PDF	6		
1437MK	\$169.00	1437K	\$173.00	9.81 x 8.81 x 4.97 [249 x 224 x 126]	PDF	9		
1437MO	\$193.00	1437O	\$198.00	12.06 x 8.81 x 4.92 [306 x 224 x 125]	PDF	12		
1437MS	\$221.00	1437S	\$226.00	12.06 x 11.06 x 4.92 [306 x 281 x 125]	PDF	16		
1437MV	\$246.00	1437V	\$253.00	14.31 x 11.06 x 4.92 [363 x 281 x 125]	PDF	20		
1437MX	\$276.00	1437X	\$285.00	14.31 x 13.31 x 4.92 [363 x 338 x 125]	PDF	25		

Note: Dimensions in inches [millimeters].

NEMA 12 and 13 Extra Deep Pushbutton



Dimensions

