

# NEMA 12 and 13 Extra Deep Pushbutton



## Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil, and water.

## Construction

- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Captive cover screws fasten into threaded, sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring (see drawings).
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

## Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray powder coating.

## Listings

- UL 508A Type 12 and 13 [UL File E65324]
- CSA Type 12 and 13 [CSA File LR21001]
- Complies with
  - NEMA Type 12 and 13
  - IEC 60529, IP54
- All appropriate components are required to maintain these standards.



NEMA 12 and 13 Extra Deep Pushbutton								
22 mm	Price	30 mm	Price	Size HxWxD	Drawing Link	# Holes	Steel Gauge	Hinged
<a href="#">1437MA</a>	\$88.00	<a href="#">1437A</a>	\$91.00	4.31 x 4.31 x 4.91 [109 x 109 x 125]	<a href="#">PDF</a>	1	16	No
<a href="#">1437MB</a>	\$102.00	<a href="#">1437B</a>	\$105.00	6.31 x 4.31 x 4.97 [160 x 109 x 126]	<a href="#">PDF</a>	2	14	Yes
<a href="#">1437MC</a>	\$116.00	<a href="#">1437C</a>	\$118.00	8.31 x 4.31 x 4.97 [211 x 109 x 126]	<a href="#">PDF</a>	3		
<a href="#">1437MD</a>	\$129.00	<a href="#">1437D</a>	\$131.00	10.31 x 4.31 x 4.97 [262 x 109 x 126]	<a href="#">PDF</a>	4		
<a href="#">1437MF</a>	\$130.00	<a href="#">1437F</a>	\$134.00	7.56 x 6.56 x 4.97 [192 x 167 x 126]	<a href="#">PDF</a>	4		
<a href="#">1437MH</a>	\$148.00	<a href="#">1437H</a>	\$152.00	9.81 x 6.56 x 4.97 [249 x 167 x 126]	<a href="#">PDF</a>	6		
<a href="#">1437MK</a>	\$169.00	<a href="#">1437K</a>	\$173.00	9.81 x 8.81 x 4.97 [249 x 224 x 126]	<a href="#">PDF</a>	9		
<a href="#">1437MO</a>	\$193.00	<a href="#">1437O</a>	\$198.00	12.06 x 8.81 x 4.92 [306 x 224 x 125]	<a href="#">PDF</a>	12		
<a href="#">1437MS</a>	\$221.00	<a href="#">1437S</a>	\$226.00	12.06 x 11.06 x 4.92 [306 x 281 x 125]	<a href="#">PDF</a>	16		
<a href="#">1437MV</a>	\$246.00	<a href="#">1437V</a>	\$253.00	14.31 x 11.06 x 4.92 [363 x 281 x 125]	<a href="#">PDF</a>	20		
<a href="#">1437MX</a>	\$276.00	<a href="#">1437X</a>	\$285.00	14.31 x 13.31 x 4.92 [363 x 338 x 125]	<a href="#">PDF</a>	25		

Note: Dimensions in inches [millimeters].

# NEMA 12 and 13 Extra Deep Pushbutton



## Dimensions

