


# NEMA 12 Screw Cover Pushbutton



## Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil, and water.

## Construction

- Formed 14-gauge steel.
- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Continuously hinged cover is secured with captive, plated steel screws which fasten into threaded sealed wells.
- Oil-resistant gasket and adhesive.
- Weldnuts are provided for mounting subpanels.
- A removable 14-gauge subpanel is included.
- A bonding stud is provided on the door and a grounding stud is provided in the enclosure.

## Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray powder coating.
- Removable subpanel is finished in RAL9003 white powder coating.

## Listings

- UL 508A Type 12 [UL File E65324]
- CSA Type 12 [CSA File LR21001]
- Complies with
  - NEMA Type 12
  - IEC 60529, IP54
- All appropriate components are required to maintain these standards.



NEMA 12 Screw Cover Pushbutton							
22 mm	Price	30 mm	Price	Console Size HxWxD	Drawing Link	# Holes	Subpanel Dimensions
<a href="#">1489MP4</a>	\$171.00	<a href="#">1489P4</a>	\$174.00	8.56 x 7.56 x 6.17 [217 x 192 x 157]	<a href="#">PDF</a>	4	6.25 x 5.25 [159 x 133]
<a href="#">1489MP6</a>	\$196.00	<a href="#">1489P6</a>	\$202.00	10.81 x 7.56 x 6.17 [275 x 192 x 157]	<a href="#">PDF</a>	6	8.50 x 5.25 [216 x 133]
<a href="#">1489MP9</a>	\$226.00	<a href="#">1489P9</a>	\$234.00	10.81 x 9.81 x 6.17 [275 x 249 x 157]	<a href="#">PDF</a>	9	8.50 x 7.50 [216 x 191]
<a href="#">1489MP12</a>	\$257.00	<a href="#">1489P12</a>	\$264.00	13.06 x 9.81 x 6.17 [332 x 249 x 157]	<a href="#">PDF</a>	12	10.00 x 7.50 [254 x 191]
<a href="#">1489MP16</a>	\$294.00	<a href="#">1489P16</a>	\$302.00	13.06 x 12.06 x 6.17 [332 x 306 x 157]	<a href="#">PDF</a>	16	10.75 x 9.75 [273 x 248]
<a href="#">1489MP20</a>	\$328.00	<a href="#">1489P20</a>	\$338.00	15.31 x 12.06 x 6.17 [389 x 306 x 157]	<a href="#">PDF</a>	20	13.00 x 9.75 [330 x 248]
<a href="#">1489MP25</a>	\$367.00	<a href="#">1489P25</a>	\$380.00	15.31 x 14.31 x 6.17 [389 x 363 x 157]	<a href="#">PDF</a>	25	13.00 x 12.00 [330 x 305]
<a href="#">1489MP30</a>	\$409.00	<a href="#">1489P30</a>	\$420.00	17.56 x 14.31 x 6.17 [446 x 363 x 157]	<a href="#">PDF</a>	30	15.25 x 12.00 [387 x 305]
<a href="#">1489MP36</a>	\$453.00	<a href="#">1489P36</a>	\$467.00	17.56 x 16.56 x 6.17 [446 x 421 x 157]	<a href="#">PDF</a>	36	15.25 x 14.25 [387 x 362]
<a href="#">1489MP42</a>	\$495.00	<a href="#">1489P42</a>	\$512.00	19.81 x 16.56 x 6.17 [503 x 421 x 157]	<a href="#">PDF</a>	42	17.50 x 14.25 [455 x 362]

Note: Dimensions in inches [millimeters].

# NEMA 12 Screw Cover Pushbutton



## Dimensions

