

NEMA 1 Galvanized Steel Screw Cover Wall-Mount



Applications

- Designed for general purpose indoor commercial use as a junction, pull or switch box.

Construction

- Formed and spot welded from 16- or 14-gauge steel depending on size.
- Flat steel covers fastened with plated steel screws.
- Keyhole slots permit cover to be lifted off without removing screws entirely.
- Through holes in back for wall-mounting.
- Grounding location embossed in body.

Finish

- Enclosure and cover are unpainted galvanized steel.

Listings

- UL-50 Type 1
[UL File 65324]
- CSA Type 1
[CSA File LR21001]
- Complies with
 - NEMA Type 1
 - IEC 60529, IP20



NEMA 1 Unpainted Galvanized Steel Junction Box Screw Cover and without Knockouts

Part Number	Price	Enclosure Size HxWxD	Drawing Link
CSG664	\$12.50	6.00 x 6.00 x 4.06 [152 x 152 x 103]	PDF
CSG666	\$16.25	6.00 x 6.00 x 6.06 [152 x 152 x 154]	PDF
CSG884	\$17.75	8.00 x 8.00 x 4.06 [203 x 203 x 103]	PDF
CSG886	\$22.00	8.00 x 8.00 x 6.06 [203 x 203 x 154]	PDF
CSG10104	\$24.50	10.00 x 10.00 x 4.06 [254 x 254 x 103]	PDF
CSG10106	\$28.50	10.00 x 10.00 x 6.06 [254 x 254 x 154]	PDF
CSG12106	\$37.00	12.00 x 10.00 x 6.06 [305 x 254 x 154]	PDF
CSG12124	\$29.50	12.00 x 12.00 x 4.06 [305 x 305 x 103]	PDF
CSG12126	\$36.50	12.00 x 12.00 x 6.06 [305 x 305 x 154]	PDF
CSG12128	\$46.00	12.00 x 12.00 x 8.06 [305 x 305 x 205]	PDF
CSG16166	\$64.00	16.00 x 16.00 x 6.06 [406 x 406 x 154]	PDF
CSG18126	\$50.00	18.00 x 12.00 x 6.06 [457 x 305 x 154]	PDF
CSG18184	\$67.00	18.00 x 18.00 x 4.06 [457 x 457 x 103]	PDF
CSG18186	\$67.00	18.00 x 18.00 x 6.06 [457 x 457 x 154]	PDF
CSG18188	\$87.00	18.00 x 18.00 x 8.06 [457 x 457 x 205]	PDF
CSG181812	\$126.00	18.00 x 18.00 x 12.06 [457 x 457 x 306]	PDF
CSG24244	\$129.00	24.00 x 24.00 x 4.06 [610 x 610 x 103]	PDF
CSG24246	\$130.00	24.00 x 24.00 x 6.06 [610 x 610 x 154]	PDF
CSG24248	\$161.00	24.00 x 24.00 x 8.06 [610 x 610 x 205]	PDF
CSG242412	\$240.00	24.00 x 24.00 x 12.06 [610 x 610 x 306]	PDF
CSG30306	\$306.00	30.00 x 30.00 x 6.10 [762 x 762 x 155]	PDF
CSG30308	\$312.00	30.00 x 30.00 x 8.10 [762 x 762 x 206]	PDF
CSG303012	\$408.00	30.00 x 30.00 x 12.10 [762 x 762 x 307]	PDF
CSG36366	\$411.00	36.00 x 36.00 x 6.10 [914 x 914 x 155]	PDF
CSG36368	\$468.00	36.00 x 36.00 x 8.10 [914 x 914 x 206]	PDF
CSG363612	\$523.00	36.00 x 36.00 x 12.10 [914 x 914 x 307]	PDF
CSG363616	\$565.00	36.00 x 36.00 x 16.10 [914 x 914 x 409]	PDF
CSG484812	\$906.00	48.00 x 48.00 x 12.10 [1219 x 1219 x 307]	PDF
CSG484816	\$997.00	48.00 x 48.00 x 16.10 [1219 x 1219 x 409]	PDF

Note: Dimensions in inches [millimeters].

NEMA 1 Galvanized Steel Screw Cover Wall-Mount



Dimensions

