

NEMA 1 Wiring Trough



Application

Designed for use as a junction box or pull box.

Construction

- Formed 16-gauge steel.
- Mounting holes on back of enclosure.
- Flat cover is secured with screws.
- Two grounding point embosses on enclosure body.

Finish

- Troughs and covers are finished in ANSI 61 gray powder coating.

Listings

- UL 870 Type 1 [cUL File E186830]
- Complies with:
 - NEMA Type 1
 - IEC 60529, IP20



NEMA 1 Wiring Trough			
Part Number	Price	Overall Size HxWxD	Drawing Link
<u>CGT1244</u>	\$25.50	4.00 x 4.00 x 12.00 [102 x 102 x 305]	<u>PDF</u>
<u>CGT1844</u>	\$38.00	4.00 x 4.00 x 18.00 [102 x 102 x 457]	<u>PDF</u>
<u>CGT2444</u>	\$40.50	4.00 x 4.00 x 24.00 [102 x 102 x 610]	<u>PDF</u>
<u>CGT3644</u>	\$55.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	<u>PDF</u>
<u>CGT4844</u>	\$70.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	<u>PDF</u>
<u>CGT1266</u>	\$39.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	<u>PDF</u>
<u>CGT1866</u>	\$45.50	6.00 x 6.00 x 18.00 [152 x 152 x 457]	<u>PDF</u>
<u>CGT2466</u>	\$56.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	<u>PDF</u>
<u>CGT3666</u>	\$79.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	<u>PDF</u>
<u>CGT4866</u>	\$102.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	<u>PDF</u>
Note: Dimensions in inches [millimeters].			