

# NEMA 3R Wiring Trough



## Application

- Designed for use to protect multiple wiring junctions in outdoor environments against the ingress of rain, sleet, snow and the external formation of ice.

## Construction

- Formed and spot welded from 14 or 16-gauge galvanized steel.
- Drip shield top design protects the enclosure against rain, snow or sleet.
- Embossed mounting holes on back of enclosure.
- Slip on removable front cover is secured with screws.
- Padlocking hasp.
- To fully comply with UL870 - 2008 requirements a bonding stud is provided on the cover and a ground stud is provided in the enclosure.
- A #10 AWG - 12 in [305 mm] grounding strap with crimped on ring terminals is also provided to comply with UL requirements.

## Finish

- Enclosure and cover are finished in ANSI 61 gray powder coating.

## Listings

- UL 870 Type 3R [UL File E186830]
- CSA Type 3R [CSA File LL21312]
- Complies with
  - NEMA Type 3R
  - IEC 60529, IP24



NEMA 3R Wiring Trough			
Part Number	Price	Enclosure Size HxDxL	Drawing Link
<a href="#">C3RWT412</a>	\$33.00	4.00 x 4.00 x 12.00 [102 x 102 x 305]	<a href="#">PDF</a>
<a href="#">C3RWT418</a>	\$50.50	4.00 x 4.00 x 18.00 [102 x 102 x 457]	<a href="#">PDF</a>
<a href="#">C3RWT424</a>	\$61.00	4.00 x 4.00 x 24.00 [102 x 102 x 610]	<a href="#">PDF</a>
<a href="#">C3RWT436</a>	\$88.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	<a href="#">PDF</a>
<a href="#">C3RWT448</a>	\$111.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	<a href="#">PDF</a>
<a href="#">C3RWT460</a>	\$139.00	4.00 x 4.00 x 60.00 [102 x 102 x 1524]	<a href="#">PDF</a>
<a href="#">C3RWT472</a>	\$167.00	4.00 x 4.00 x 72.00 [102 x 102 x 1829]	<a href="#">PDF</a>
<a href="#">C3RWT612</a>	\$53.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	<a href="#">PDF</a>
<a href="#">C3RWT624</a>	\$83.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	<a href="#">PDF</a>
<a href="#">C3RWT618</a>	\$85.00	6.00 x 6.00 x 18.00 [152 x 152 x 457]	<a href="#">PDF</a>
<a href="#">C3RWT636</a>	\$113.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	<a href="#">PDF</a>
<a href="#">C3RWT660</a>	\$180.00	6.00 x 6.00 x 60.00 [152 x 152 x 1524]	<a href="#">PDF</a>
<a href="#">C3RWT672</a>	\$217.00	6.00 x 6.00 x 72.00 [152 x 152 x 1829]	<a href="#">PDF</a>
<a href="#">C3RWT648</a>	\$151.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	<a href="#">PDF</a>
<a href="#">C3RWT812</a>	\$89.00	8.00 x 8.00 x 12.00 [203 x 203 x 305]	<a href="#">PDF</a>
<a href="#">C3RWT824</a>	\$138.00	8.00 x 8.00 x 24.00 [203 x 203 x 610]	<a href="#">PDF</a>
<a href="#">C3RWT836</a>	\$167.00	8.00 x 8.00 x 36.00 [203 x 203 x 914]	<a href="#">PDF</a>
<a href="#">C3RWT848</a>	\$215.00	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	<a href="#">PDF</a>
Note: Dimensions in inches [millimeters].			

NEMA 3R Wiring Trough			
Part Number	Price	Enclosure Size HxDxL	Drawing Link
<a href="#">C3RWT860</a>	\$251.00	8.00 x 8.00 x 60.00 [203 x 203 x 1524]	<a href="#">PDF</a>
<a href="#">C3RWT872</a>	\$287.00	8.00 x 8.00 x 72.00 [203 x 203 x 1829]	<a href="#">PDF</a>
<a href="#">C3RWT896</a>	\$390.00	8.00 x 8.00 x 96.00 [203 x 203 x 2438]	<a href="#">PDF</a>
<a href="#">C3RWT8116</a>	\$492.00	8.00 x 8.00 x 116.00 [203 x 203 x 2946]	<a href="#">PDF</a>
<a href="#">C3RWT1024</a>	\$221.00	10.00 x 10.00 x 24.00 [254 x 254 x 610]	<a href="#">PDF</a>
<a href="#">C3RWT1036</a>	\$249.00	10.00 x 10.00 x 36.00 [254 x 254 x 914]	<a href="#">PDF</a>
<a href="#">C3RWT1048</a>	\$281.00	10.00 x 10.00 x 48.00 [254 x 254 x 1219]	<a href="#">PDF</a>
<a href="#">C3RWT1060</a>	\$353.00	10.00 x 10.00 x 60.00 [254 x 254 x 1524]	<a href="#">PDF</a>
<a href="#">C3RWT1072</a>	\$399.00	10.00 x 10.00 x 72.00 [254 x 254 x 1829]	<a href="#">PDF</a>
<a href="#">C3RWT1096</a>	\$532.00	10.00 x 10.00 x 96.00 [254 x 254 x 2438]	<a href="#">PDF</a>
<a href="#">C3RWT10116</a>	\$664.00	10.00 x 10.00 x 116.00 [254 x 254 x 2946]	<a href="#">PDF</a>
<a href="#">C3RWT1224</a>	\$304.00	12.00 x 12.00 x 24.00 [305 x 305 x 610]	<a href="#">PDF</a>
<a href="#">C3RWT1236</a>	\$323.00	12.00 x 12.00 x 36.00 [305 x 305 x 914]	<a href="#">PDF</a>
<a href="#">C3RWT1248</a>	\$346.00	12.00 x 12.00 x 48.00 [305 x 305 x 1219]	<a href="#">PDF</a>
<a href="#">C3RWT1260</a>	\$397.00	12.00 x 12.00 x 60.00 [305 x 305 x 1524]	<a href="#">PDF</a>
<a href="#">C3RWT1272</a>	\$462.00	12.00 x 12.00 x 72.00 [305 x 305 x 1829]	<a href="#">PDF</a>
<a href="#">C3RWT1284</a>	\$539.00	12.00 x 12.00 x 84.00 [305 x 305 x 2134]	<a href="#">PDF</a>
<a href="#">C3RWT1296</a>	\$616.00	12.00 x 12.00 x 96.00 [305 x 305 x 2438]	<a href="#">PDF</a>
<a href="#">C3RWT12116</a>	\$777.00	12.00 x 12.00 x 116.00 [305 x 305 x 2946]	<a href="#">PDF</a>
Note: Dimensions in inches [millimeters].			