

NEMA 4 and 4X Stainless Steel Pushbutton Wall-Mount



Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil and large amounts of water from any angle, or where highly corrosive conditions exist.

Construction

- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Captive stainless steel cover screws thread into sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring.
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door, and a grounding stud is provided on the enclosure.

Finish

- Natural stainless steel with a #4 smooth brushed finish.

Listings

- UL 508A Type 4 and 4X [UL File E65324]
- CSA Type 4 and 4X [CSA File R21001]
- Complies with
 - NEMA Type 3R, 4 and 4X
 - IEC 60529, IP66
- All appropriate components are required to maintain these standards.



NEMA 4 and 4X Stainless Steel Pushbutton Wall-Mount												
304 Stainless Steel				316 Stainless Steel				Size HxWxD	Drawing Link	# Holes	Steel Gauge	Hinged
22 mm	Price	30 mm	Price	22 mm	Price	30 mm	Price					
1435MSSA	\$176.00	1435SSA	\$173.00	1435MS16A	\$220.00	1435S16A	\$218.00	3.81 x 3.56 x 2.91 [97 x 90 x 74]	PDF	1	16	No
1435MSSB	\$207.00	1435SSB	\$204.00	1435MS16B	\$260.00	1435S16B	\$258.00	6.06 x 3.56 x 2.91 [154 x 90 x 74]	PDF	2		
1435MSSC	\$240.00	1435SSC	\$235.00	1435MS16C	\$301.00	1435S16C	\$297.00	8.31 x 3.56 x 2.92 [211 x 90 x 74]	PDF	3		
1435MSSD	\$271.00	1435SSD	\$274.00	1435MS16D	\$341.00	1435S16D	\$337.00	10.56 x 3.56 x 2.92 [268 x 90 x 74]	PDF	4		
1435MSSH	\$364.00	1435SSH	\$359.00	1435MS16H	\$450.00	1435S16H	\$444.00	9.81 x 6.56 x 3.22 [249 x 167 x 82]	PDF	6	14	Yes
1435MSSK	\$430.00	1435SSK	\$424.00	1435MS16K	\$534.00	1435S16K	\$527.00	9.81 x 8.81 x 3.22 [249 x 224 x 82]	PDF	9		
1435MSSO	\$492.00	1435SSO	\$486.00	1435MS16O	\$611.00	1435S16O	\$602.00	12.06 x 8.81 x 3.22 [306 x 224 x 82]	PDF	12		

Note: Dimensions in inches [millimeters].

NEMA 4 and 4X Stainless Steel Pushbutton Wall-Mount



Dimensions

