

NEMA 1, 4, 4X, and 12 Stainless Steel Wiring Trough



Applications

Designed to enclose and protect multiple wiring junctions from dirt, dust, oil and water while providing a measure of corrosion protection.

Construction

- Formed 14 gauge 304 stainless steel.
- Smooth continuously welded seams.
- Butt hinged cover is secured with easily operated screw clamps.
- Oil resistant gaskets are permanently secured.
- 12 gauge external mounting feet are welded to the back.

Finish

Troughs and covers are natural stainless steel with a smooth brushed finish.

Listings

- UL 870 Type 1, 4, 4X, and 12 [File E186830]
- CSA Type 1, 4, 4X, and 12
- Complies with
 - NEMA Type 1, 4, 4X, and 12
 - IEC 60529, IP66

NEMA 1, 4, 4X, and 12 Wiring Trough			
Part Number	Price	Overall Size HxWxD	Drawing Link
1486B12SS	\$331.00	2.50 x 2.50 x 12.00 [64 x 64 x 305]	PDF
1486B18SS	\$357.00	2.50 x 2.50 x 18.00 [64 x 64 x 457]	PDF
1486B24SS	\$384.00	2.50 x 2.50 x 24.00 [64 x 64 x 610]	PDF
1486B36SS	\$435.00	2.50 x 2.50 x 36.00 [64 x 64 x 914]	PDF
1486B48SS	\$488.00	2.50 x 2.50 x 48.00 [64 x 64 x 1219]	PDF
1486B60SS	\$538.00	2.50 x 2.50 x 60.00 [64 x 64 x 1524]	PDF
1486B72SS	\$585.00	2.50 x 2.50 x 72.00 [64 x 64 x 1829]	PDF
1486C12SS	\$387.00	4.00 x 4.00 x 12.00 [102 x 102 x 305]	PDF
1486C18SS	\$435.00	4.00 x 4.00 x 18.00 [102 x 102 x 457]	PDF
1486C24SS	\$485.00	4.00 x 4.00 x 24.00 [102 x 102 x 610]	PDF
1486C30SS	\$535.00	4.00 x 4.00 x 30.00 [102 x 102 x 762]	PDF
1486C36SS	\$579.00	4.00 x 4.00 x 36.00 [102 x 102 x 914]	PDF
1486C48SS	\$702.00	4.00 x 4.00 x 48.00 [102 x 102 x 1219]	PDF
1486C60SS	\$800.00	4.00 x 4.00 x 60.00 [102 x 102 x 1524]	PDF
1486C72SS	\$875.00	4.00 x 4.00 x 72.00 [102 x 102 x 1829]	PDF
1486D12SS	\$457.00	6.00 x 6.00 x 12.00 [152 x 152 x 305]	PDF
1486D18SS	\$529.00	6.00 x 6.00 x 18.00 [152 x 152 x 457]	PDF
1486D24SS	\$604.00	6.00 x 6.00 x 24.00 [152 x 152 x 610]	PDF
1486D30SS	\$674.00	6.00 x 6.00 x 30.00 [152 x 152 x 762]	PDF
1486D36SS	\$749.00	6.00 x 6.00 x 36.00 [152 x 152 x 914]	PDF
1486D48SS	\$894.00	6.00 x 6.00 x 48.00 [152 x 152 x 1219]	PDF
1486D60SS	\$1,075.00	6.00 x 6.00 x 60.00 [152 x 152 x 1524]	PDF
1486D72SS	\$1,226.00	6.00 x 6.00 x 72.00 [152 x 152 x 1829]	PDF
1486E12SS	\$562.00	8.00 x 8.00 x 12.00 [203 x 203 x 305]	PDF
1486E24SS	\$742.00	8.00 x 8.00 x 24.00 [203 x 203 x 610]	PDF
1486E36SS	\$947.00	8.00 x 8.00 x 36.00 [203 x 203 x 914]	PDF
1486E48SS	\$1,180.00	8.00 x 8.00 x 48.00 [203 x 203 x 1219]	PDF
1486E60SS	\$1,386.00	8.00 x 8.00 x 60.00 [203 x 203 x 1524]	PDF
1486G24SS	\$1,031.00	12.00 x 12.00 x 24.00 [305 x 305 x 610]	PDF
1486G36SS	\$1,327.00	12.00 x 12.00 x 36.00 [305 x 305 x 914]	PDF
1486G48SS	\$1,674.00	12.00 x 12.00 x 48.00 [305 x 305 x 1219]	PDF
1486G60SS	\$1,933.00	12.00 x 12.00 x 60.00 [305 x 305 x 1524]	PDF

Note: Dimensions in inches [millimeters].

